

Main

Enclosure type	Distribution enclosure
Range of product	Pragma
Device short name	Pragma
Accessories included with enclosure	3 terminal blocks Blanking plate strip Identification label Marking kit

Complementary

Enclosure mounting	Surface
[In] rated current	90 A
Number of horizontal rows	1
Number of 18 mm modules per row	18
Total number of 18 mm modules	18
Type of rail	DIN
Cable entry	Cable or tube Cut-out plates Removable plates Trunking
Comb busbar and distribution block compatibility	XE compatible
Number of terminal blocks	Earth: 1 Quick with 17 outgoing Phase / neutral: 2 Quick with 6 outgoing
Distribution block outgoing	1 x 25 mm ² for earth 2 x 50 mm ² for phase / neutral 10 x 25 mm ² for phase / neutral 16 x 6 mm ² for earth
Power dissipation in W	33 W
Enclosure material	Back part: technoplastic Front face: technoplastic
Width	426 mm
Height	300 mm
Depth	125 mm
Colour	Enclosure : titanium white

Environment

Standards	EN 60439-3 EN 60695-2-11 IEC 60439-3 IEC 60529 IEC 60695-2-11 IEC 60947-7-1 IEC 62262
Fire resistance	Back part: 750 °C conforming to IEC 60695-2-1 Front face: 750 °C conforming to IEC 60695-2-1
IP degree of protection	IP30 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262
Electrical shock protection class	Class II
Ambient air temperature for operation	-25...60 °C

RoHS EUR conformity date	0810
RoHS EUR status	Compliant
