



Switches > Toggle Switches



Contact Current Rating: **.4 A**

Configuration (Pole-Throw): **Single Pole - Double Throw**

Operating Function: **On On**

Number of Positions: **2**

Operating Voltage: **20 VDC**

Features

Product Type Features

Sealed Device	Yes
Switch Connection Type	Wire Wrap
Toggle Style	Baton Standard
Switch Type	Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On On
Number of Positions	2

Electrical Characteristics

Contact Current Rating	.4 A
Operating Voltage	20 VAC

Body Features

Case Color	Red
Product Orientation	Vertical
Bushing Style	Threaded
Bushing Thread Size	10-48

Contact Features

Switch Contact Plating Material	Gold
---------------------------------	------

Mechanical Attachment



Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Process Sealed	No
----------------	----

Dimensions

Toggle Length	7.37 mm[.29 in]
---------------	-----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #5746613-1
08 DIP PLUG CONN-W/COVER



TE Part #5227079-5
COMM BNC PLUG



TE Part #171551-1
P.G SPADE




TE Part #552272-1
ASSY, PLUG, 24 POS, B SLOT



TE Part #5-1625999-0
HSC100 R10 5%



TE Part #2267079-3
TMS1T3B1M1QE



TE Part #9-160463-5
FASTON, PGYBCK, PIDG, PH BR, .250, 16-14



TE Part #1-2176093-3
RP 2A 0.25W 12K4 0.1% 25PPM 1K RL



TE Part #NB17372001
RP-4800-NO.2-0-STK



TE Part #5787422-1
HDR ASY,RA,RKEY,STR TAIL,12.0V

Documents

Product Drawings

TMS1T3B1M5RE

English

CAD Files

Customer View Model

ENG_CVM_CVM_2267079-1_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2267079-1_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2267079-1_A1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Subminiature Switches

English