



AVB 3,2/2/12

Short circuit proof PCB transformer

- Maximum power from minimum size
- Vacuum resin moulded (self extinguishing to UL 94 V-0)

Short circuit proof safety isolating transformer to IEC 61558-2-6, DIN EN 61558-2-6, VDE 0570 part 2-6

*Transformer to IEC 61558-2-1, DIN EN 61558-2-1, VDE 0570 part 2-1 (without VDE-Approval)



AVB 3,2/2/12

Short circuit proof PCB transformer



Input data

Input voltage	2x115 V
Frequency range	50 - 60 Hz
No-load loss (typ.)	0.5 W

Output data

Output voltage	2x12 V
No-load voltage (ca. x factor)	1.57
Efficiency	58 %
Power	3.20 VA

Standards and security

Approvals	C-UL-US, ENEC 10 (VDE)
Protection index	IP 00
Safety class (prepared)	I
Ambient temperature max.	50 °C
Class of Insulation System	VDE=E, UL=105
Test voltage	5000 V, 50 Hz

Mechanical data

Type	encapsulated
Core type	EI 38/16,5
Terminals	Pins for printed circuit boards
Pin (∅)	0,6 x 0,8
Wide	35 mm
Height	30.8 mm
Depth	41 mm
Weight	0.17 g

Order numbers

Order Number	AVB 3,2/2/12
--------------	--------------

BLOCK Transformatoren-Elektronik GmbH

Max-Planck-Straße 36-46

27283 Verden

Germany

Phone +49 4231 678-0

Fax +49 4231 678-177