



PORT-ROLL

POLYCHOC WHEEL



STRONG POINTS

- ↳ Wheelability on smooth surfaces
- ↳ Low starting effort.

APPLICATIONS

Standard materials handling on hard surfaces but which are in good condition.

CASTOR ASSEMBLY: • Swivel or fixed. • Pressed steel. • Fastening by top plate. • Swivels on two rows of balls. • Bright zinc-plated protection.

WHEEL: • Polychoc: white impact-resistant polyolefine one-piece wheel. • Plain bearing. • Bolted axle (except for diameters 50 mm and 65 mm, riveted axle).

LOCKING: • **MB** meta-bloc: double action adjustable rear brake: wheel and swivel. • Steel pedal.

Icon	Icon	Icon	Icon	Icon	Icon	Icon	Icon	Icon	Type	Icon	Code	EAN 13	
50	22	67	30	15	67x48	55x30	6,5	50	Swivel	MB	0,155	108 0105	339680 606010 0
									Fixed	MB	0,145	508 0105	339680 606011 7
65	27	86	36	23	75x60	55x40	7	65	Swivel	MB	0,225	108 0205	339680 606020 9
									Fixed	MB	0,175	508 0205	339680 606021 6
80	30	107	40	33	105x80	80x60	9	80	Swivel	MB	0,560	127 0304	339680 607028 4
									Swivel	MB	0,740	1 275 0304	339680 607034 5
									Fixed	MB	0,340	508 0304	339680 607029 1
100	32	130	46	42	105x80	80x60	9	100	Swivel	MB	0,655	127 0405	339680 606040 7
									Swivel	MB	0,745	1 275 0405	339680 606041 4
									Fixed	MB	0,400	508 0405	339680 606042 1
125	37	158	46	45	105x80	80x60	9	125	Swivel	MB	0,780	216 1015	339680 606050 6
									Swivel	MB	0,880	2 170 1015	339680 606052 0
									Fixed	MB	0,475	516 1015	339680 606053 7

Top-plated materials handling castors