

CUC-V06-F1PBK-S/UBA/UBB - Panel-mount frame



1409117

<https://www.phoenixcontact.com/gb/products/1409117>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel-mount frame, degree of protection: IP65/IP67

Commercial data

Item number	1409117
Packing unit	5 pc
Minimum order quantity	5 pc
Note	Made to order (non-returnable)
Sales key	ABNNFC
Product key	ABNNFC
GTIN	4046356862219
Weight per piece (including packing)	18.16 g
Weight per piece (excluding packing)	18.16 g
Customs tariff number	85366990
Country of origin	DE

CUC-V06-F1PBK-S/UBA/UBB - Panel-mount frame



1409117

<https://www.phoenixcontact.com/gb/products/1409117>

Technical data

Product properties

Product type	Panel-mount frame
--------------	-------------------

Electrical properties

Transmission medium	Copper
---------------------	--------

Dimensions

Dimensional drawing	
Width	36 mm
Height	36 mm
Length	46.6 mm

Material specifications


Flammability rating according to UL 94	V0
Seal material, flat gasket	NBR

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP65/IP67

Drawings

Dimensional drawing




Mounting cutout

1409117


<https://www.phoenixcontact.com/gb/products/1409117>

Schematic diagram



Pin assignment socket USB, type A

Schematic diagram



Pin assignment socket USB, type B

CUC-V06-F1PBK-S/UBA/UBB - Panel-mount frame



1409117

<https://www.phoenixcontact.com/gb/products/1409117>

Classifications

ECLASS

ECLASS-13.0	27440390
-------------	----------

ETIM

ETIM 9.0	EC004746
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------