

LOCTITE® MR 5921™Known as LOCTITE® 5921™
August 2015**PRODUCT DESCRIPTION**

LOCTITE® MR 5921™ provides the following product characteristics:

Technology	Solvent based
Chemical Type	Resin / Isopropanol / Fillers
Appearance	Red brown viscous paste ^{LMS}
Components	One part - requires no mixing
Viscosity	Very high
Cure	Solvent evaporation
Application	Sealing
Product Benefits	• Extends gasket life • Prevents leaks • Fast drying • Hard setting

LOCTITE® MR 5921™ is a reddish brown, viscous, fast drying paste that changes to a hard, semi flexible seal through solvent evaporation. It seals flanges, fittings, connections and assemblies against leakage.

Typical applications include freeze plugs, industrial sealant for permanent assemblies, threaded connections, manifold gaskets, air ducts, boilers, pipe fittings and plumbing connections

TYPICAL PROPERTIES OF UNCURED MATERIAL

Specific Gravity @ 25 °C 1.6

Viscosity, Brookfield - RVT, 25 °C, mPa·s (cP):
Spindle 7., speed 5 rpm 500,000 to 700,000

Flash Point - See SDS

TYPICAL CURING PERFORMANCE

LOCTITE® MR 5921™, once applied, develops a hard, semi-flexible sealant by solvent evaporation. Dry times will vary with temperature, humidity and gap.

Chemical/Solvent Resistance

LOCTITE® MR 5921™ retains effective properties in contact with water, ethylene glycol, gasoline, motor oil, transmission fluid and sea water.

GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Safety Data Sheet (SDS).

Directions for use:

1. Remove all previous material from mating surfaces.
2. For best results, clean and dry all surfaces with a residue-free solvent.
3. Remove cap, puncture tube (using self-piercing cap) or cartridge seal and attach extension nozzle (if provided).
4. When used as a gasket dressing, spread product with a spatula to a uniform film on one side of gasket and then position it on the assembly. Coat the second side of gasket and re-assemble.
5. Assembly is operational after 2 hours, full cure is effective after 24 hours.

Clean-up

1. LOCTITE® MR 5921™ can be removed from metal surfaces with isopropanol. If the sealant has been dried for a long time or at high temperatures, cover the sealant with alcohol and allow to soften overnight.
2. Clean hands with hand cleaners.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties. Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.0

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.