

Specifications

Eaton EVMAF332A

Eaton Managed G4 Rack PDU, 0U, 39U, IEC-60309 input, 3m cord, 3ph, 22kW, 32A, 415/240V, 24 outlets (12)C13, (12)C39



General specifications

PRODUCT NAME	Eaton Rack PDU G4
CATALOG NUMBER	EVMAF332A
MODEL CODE	PDU G4 MA 0U 309 32A 3P 12xC13,12xC39
EAN	3553340696978
PRODUCT LENGTH/DEPTH	1730 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	52 mm
PRODUCT WEIGHT	5.8 kg
COMPLIANCES	CB LVD Directive RoHS Directive WEEE Directive Packaging Directive EMC Directive
CERTIFICATIONS	IEC 62368-1 EN IEC 63000 CE EAC UKCA Cm Ukr IEC/EN 61000-6-2 IEC/EN 61000-6-4 CISPR 35/EN 55035 IEC 61000-3-11 IEC 61000-3-12



Powering Business Worldwide

Electrical input

INPUT CONNECTION	IEC-60309 32A 3Ph
WATTAGE	22 kW max
AMPERAGE RATING	32 A
INPUT VOLTAGE	240/415V
PHASE	Three-phase
CIRCUIT BREAKER	(6) single-pole
FREQUENCY RATING	50/60 Hz
CORD LENGTH	3m

Electrical output

OUTLETS	(12) C13, (12) C39
NUMBER OF OUTPUTS C13	12
NUMBER OF OUTPUTS C19	12
NUMBER OF OUTPUTS (OTHER)	12
NUMBER OF OUTLETS WITH EARTH PIN	24

Technology & communications

TYPE Managed Rack PDU

OUTLET CONTROL Yes

SPECIAL FEATURES

- Remote Site Management
- Versatile C39 outlet supports C14 or C20 power cord plug
- High retention outlets designed to securely fit standard power cords and support P-Lock power cords
- Cybersecurity standards UL 2900-1 and IEC 62443-4-2
- Hot-Swap network control module
- Network Cascading, connect up to 32 PDUs via network loop
- Power sharing between two network modules PDUs ensures constant access to PDU data & sensors
- 1% IEC Class 1 billing grade measurement accuracy
- Gigabit network card with 2x Gb ports
- Support protocols RestAPI, Modbus TCP, SNMP, LDAP, HTTPS
- 1% measurement accuracy at the outlet level (V, W, A)
- Outlets control for On/Off, reboot, and sequential start-up capabilities

ETHERNET INTERFACE Yes

SERIAL INTERFACE Yes

Additional specifications

OPERATING TEMPERATURE 0° to 60°C (32° to 140°F)

ACCESSORIES

- Rack PDU
- Rack mounting accessories
- Quickstart guide
- Safety Instructions

MATERIAL Aluminium

COLOR Black

SNMP	Yes
MASS CONFIGURATION	Yes

Resources

BROCHURES	Rack PDU G4 Brochure EN
DECLARATIONS OF CONFORMITY	EU declaration of conformity Rack PDU G4
DRAWINGS	EVMAF332A-en-us

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

