



**Technical Data:**

Switch type: 1pole on/off, can be illuminated  
2pole on/off, can be illuminated  
1pole change-over  
2pole change-over

Switching capacity: ~ 6 (3) A 250 V, T 125  
~ 10 (4) A 250 V, T 125

Contact opening: > 3.0 mm

Neon lamp: with resistor for 220 V~, T 100, 30 000 h

Life: at least 10 000 switching cycles at maximum voltage and current load

Protection class: for device of protection class II

Connection: fast-on terminals 6.3 x 0.8

Fixing: clamping device for panel thickness 0.6 – 2.0 mm

Execution: housing and rocker: black, white, brown, colour combinations  
marking: coloured according to specification  
signal cap: can be illuminated, red, yellow, green

Material: housing: thermosetting plastic  
frame and knob: thermoplastic PA 66  
contacts: CuZn with Ag and E-Cu

Further executions: on request

**Connection:**

Fast-on terminal 6.3 x 0.8	Fast-on terminal 4.8 x 0.8	Fast-on terminal 4.8 x 0.8	Fast-on terminal 2.8 x 0.5	Screw terminal M 3.5 x 6	Solder links	Tong contact solderable	Solder-eye	Solder tag for printed circuits	Solder tag for printed circuits	Crimp connection
●										

**Approval:**

CB	●									
----	---	--	--	--	--	--	--	--	--	--