


NO	DESCRIPTION	DATE
△	BACKGROUND FORMAT UPDATED	03.22.04
△	BACKGROUND FORMAT UPDATED	01.07.09'
△	DEL INTERFACE -65°C TO +165° C → -40°C TO +70° C	08.16.10'
△	ADD DC RESISTANCE ADD POWER RATING	05.09.12'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-1 GHz
 1.2 NOMINAL IMPEDANCE: 75 OHM
 1.3 DC RESISTANCE: 75 OHMS±1% △
 1.4 POWER RATING: 0.5W △

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
 2.2 CENTER CONTACT: BRASS PER JIS-C3604
 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -40° C TO +70° C △

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
10	CHASSIS	BRASS	1	SILVER 70 μ" MIN.
9	RESISTOR	1/2W-75Ω	1	±1%
8	BODY	BRASS	1	SILVER 70 μ" MIN.
7	WASHER	BRASS	1	SILVER 70 μ" MIN.
6	SPRING WASHER	SK-5	1	NICKEL
5	WASHER	BRASS	1	NICKEL
4	GASKET	SILICONE	1	RED
3	CENTER CONTACT	BRASS	1	SILVER 70 μ" MIN.
2	INSULATION	TEFLON	1	NONE
1	SHELL	BRASS	1	SILVER 70 μ" MIN.

APPROVED by _____ DATE: _____



DESCRIPTION		BNC STRAIGHT PLUG TERMINATOR					
製圖	DRAWN	TOLERANCE	品名	13-52-4 T.S.S	DATE	版次	REV.
	Yoko		TITLE	\ROHS COMPLIANT (75Ω)			
檢圖	CHECK	TOLERANCE	單位	DWG.NO.	13-0466		
	Ivan		mm(in)				
認定	APPROVAL	TOLERANCE	比例	SCALE			
	Angela		ANGLE ±5°				