

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



PCB terminal block, Nominal current: 41 A, Nom. voltage: 320 V, Pitch: 7.5 mm, Number of positions: 1, Connection method: Screw connection with tension sleeve, Mounting: Wave soldering, Conductor/PCB connection direction: 0 °, Color: green, The article can be aligned to create different nos. of positions!

Why buy this product

- ${\ensuremath{\,^{\scriptstyle\blacksquare}}}$ Well-known connection principle allows worldwide use
- ☑ Low temperature rise, thanks to maximum contact force
- ☑ Allows connection of two conductors
- Potentials can be easily looped through with additional connection to the PCB
- Two solder pins reduce the mechanical strain on the soldering spots



Key Commercial Data

Packing unit	50 STK
Minimum order quantity	50 STK
GTIN	4 017918 040918
GTIN	4017918040918
Weight per Piece (excluding packing)	5.250 g
Custom tariff number	85369010
Country of origin	Poland

Technical data

Dimensions

Length	20.6 mm
Pitch	7.5 mm
Width	7.50 mm
Constructional height	18 mm
Height	23 mm
Solder pin [P]	5 mm



Technical data

Dimensions

Pin dimensions	0,9 x 0,9 mm		
Hole diameter	1.3 mm		
General			
Range of articles	KDS 4		
Insulating material group	1		
Rated surge voltage (III/3)	4 KV		
Rated surge voltage (III/2)	4 kV		
Rated surge voltage (II/2)	4 kV		
Rated voltage (III/3)	320 V		
Rated voltage (III/2)	320 V		
Rated voltage (II/2)	630 V		
Connection in acc. with standard	EN-VDE		
Nominal current I _N	41 A		
Nominal cross section	4 mm ²		
Maximum load current	41 A (with 6 mm ² conductor cross section)		
Insulating material	PA		
Solder pin surface	Sn		
Flammability rating according to UL 94	V0		
Internal cylindrical gage	A3		
Stripping length	8 mm		
Number of positions	1		
Screw thread	M3		
Tightening torque, min	0.6 Nm		
Tightening torque max	0.8 Nm		
Connection data			
Conductor cross section solid min.	0.2 mm ²		
Conductor cross section solid max.	6 mm²		
Conductor cross section flexible min.	0.2 mm ²		
Conductor cross section flexible max.	4 mm ²		
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.25 mm ²		
Conductor cross section flexible, with ferrule without plastic sleeve max.	4 mm ²		

Conductor cross section flexible, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	4 mm²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	10
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1 mm ²



Technical data

Connection data

2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	2.5 mm ²


Standards and Regulations

Connection in acc. with standard	EN-VDE
	CSA
Flammability rating according to UL 94	V0


Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50	
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"	

Drawings



Dimensional drawing



Approvals

Approvals

Approvals

CSA / SEV / RS / CCA / EAC / cULus Recognized / DNV GL

Ex Approvals

Approval details



Approvals

CSA	SP.	http://www.csagroup.org/services/testing- and-certification/certified-product-listing/			13631
		В		D	
mm²/AWG/kcmil		28-10		28-10	
Nominal current IN		30 A		10 A	
Nominal voltage UN		300 V		300 V	
SEV		https://www.electro	osuisse.ch/en/meta/sho	p/product-certificates.html	IK-3248
mm²/AWG/kcmil			6		
Nominal voltage UN			400 V		
RS		http:	//www.rs-head.spb.ru/e	n/index.php	10.04059.250
CCA					IK-3249
mm²/AWG/kcmil			6		
Nominal voltage UN			400 V		
EAC	EAC				B.01742
cULus Recognized	c AL us		n/cgi-bin/XYV/template	/LISEXT/1FRAME/index.htm	E60425-19770427
		В		D	
mm²/AWG/kcmil		30-10		30-10	
Nominal current IN		30 A		10 A	
Nominal voltage UN		300 V		300 V	

Phoenix Contact 2017 © - all rights reserved http://www.phoenixcontact.com