

Part Number : 731010360

Product Description : BNC Jack, Straight, PCB Receptacle, Through Hole, Die Cast Body, Nickel (Ni) Plated, Overall Length 23.90mm, 75 Ohms

Series Number : 73171

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

731010360_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73171
Description	BNC Jack, Straight, PCB Receptacle, Through Hole, Die Cast Body, Nickel (Ni) Plated, Overall Length 23.90mm, 75 Ohms
Product Name	BNC
Style	PCB
Type	Miniature
UPC	756054371923

Electrical

Frequency	2 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	1.853/g
Orientation	Straight
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A

PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Reverse Polar	No
Wire/Cable Type	N/A

This document was generated on Aug 06, 2025