

Technical data



1206SK

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, tapered bore, open

VISUAL (S)



1206SK

Double-row self-aligning ball bearings

PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	30 mm
D - External diameter	62 mm
B - Bearing/Inner ring width	16 mm
rs - Min fillet radius	1 mm
Associated sleeve reference	H206X
Radial clearance class	CN
Precision class	P0
Mass	0,22 kg

PRODUCT PERFORMANCE	
C - Dynamic load	15800000 mN
C0 - Static load	4650000 mN
Cu - Fatigue limit load	190000 mN
e - Coefficient	0.25
Y0 - Static axial load coefficient	2.6
Y1 - Lower axial load coefficient	2.5
Y2 - Upper axial load coefficient	3.9
N lim - Oil lubrication limit speed	72000 °/s
N lim - Grease lubrication limit speed	60000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT	
da min - Min shoulder diameter IR	35 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

1206SK

Double-row self-aligning ball bearings

ABUTMENT	
da max - Max shoulder diameter IR	39 mm
db - Min diameter for Sleeve	33 mm
Ce - Min length fro Sleeve	5 mm
Da max - Max shoulder diameter OR	57 mm
ra max - Max shaft & housing fillet radius	1 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15