

PCAN-GPS FD

Programmable Sensor Module with CAN FD Connection

The PCAN-GPS FD is a programmable sensor module for position and orientation determination with CAN FD connection. It has a satellite receiver, a magnetic field sensor, an accelerometer, and a gyroscope. Incoming sensor data is processed by the NXP microcontroller LPC54618 and then transmitted via CAN or CAN FD.

The behavior of the PCAN-GPS FD can be programmed freely for specific applications. The firmware is created using the included development package with GNU compiler for C and C++ and is then transferred to the module via CAN. Various programming examples facilitate the implementation of own solutions.

On delivery, the PCAN-GPS FD is provided with a standard firmware that transmits the raw data of the sensors periodically on the CAN bus.



Specifications

- ___ NXP LPC54618 microcontroller with Arm® Cortex® M4 core
- ___ High-speed CAN connection (ISO 11898-2)
 - Complies with CAN specifications 2.0 A/B and FD
 - CAN FD bit rates for the data field (64 bytes max.) from 40 kbit/s up to 10 Mbit/s
 - CAN bit rates from 40 kbit/s up to 1 Mbit/s
 - NXP TJA1043 CAN transceiver
- ___ CAN termination can be activated through solder jumpers
- ___ Wake-up by CAN bus or by separate input
- ___ Receiver for navigation satellites u-blox MAX-M10S
 - Supported navigation and supplementary systems: GPS, Galileo, BeiDou, GLONASS, SBAS, and QZSS
 - Simultaneous reception of 4 navigation systems
 - 3.3 V supply for active GPS antennas
- ___ Electronic three-axis magnetic field sensor IIS2MDC from ST
- ___ Gyroscope and three-axis accelerometer ISM330DLC from ST
- ___ 8 MByte QSPI flash
- ___ 3 digital I/Os, each usable as input (High-active) or output with Low-side switch
- ___ LEDs for status signaling
- ___ Connection via a 10-pole terminal strip (Phoenix)
- ___ Voltage supply from 8 to 32 V
- ___ Button cell for preserving the RTC and the GPS data to shorten the TTFF (Time To First Fix)
- ___ Extended operating temperature range from -40 to +85 °C (-40 to +185 °F) (with exception of the button cell)
- ___ New firmware can be loaded via CAN interface

Ordering information

Designation	Part No.
PCAN-GPS FD	IPEH-003110

Scope of supply

- ___ PCAN-GPS FD in plastic casing including mating connector
- ___ External antenna for satellite reception
- ___ Windows development package with GCC ARM Embedded, flash program, and programming examples
- ___ Manual in PDF format

Requirements

- ___ The transfer of the firmware via CAN requires a PEAK CAN interface