

# NON-SPARKING HACK SAW



EGAMaster non-sparking hacksaw are ideal for cutting applications in potentially explosive environments, such as oil platforms, petrochemicals, shipbuilding, etc.



**1.** With a hardness of 311-408 Brinell (Cu-Be) and 241-311 Brinell (Al-Bron).

**2.** Ergonomic and non-slip handle for superior grip and maximum safety.



## HACK SAW

| COD.         | MAT.  | COD.         | MAT.    | L (mm) |     |
|--------------|-------|--------------|---------|--------|-----|
| <b>72220</b> | Cu-Be | <b>72221</b> | Al-Bron | 500    | 600 |



## BLADES FOR HACK SAW

| COD.         | MAT.  | L (mm) |    |    |
|--------------|-------|--------|----|----|
| <b>72223</b> | Cu-Be | 300    | 18 | 35 |



**Cu-Be** Beryllium copper  
**Al-Bron** Aluminium bronze