



SITOR fuse link, with blade contacts, NH2L, In: 400 A, gR, Un DC: 900 V, front indicator

Model			
product brand name		SENTRON	
product designation		SITOR fuse link	
design of the product		with blade contacts without slots	
design of an identification indicator		front indicator	
design of the switching contact		with blade contacts for mounting in LV HRC fuse bases	
design of the fuse link		Parallel SITOR semiconductor fuse, LV HRC design	
General technical data			
size of fuse system according to EN 60269-1		NH2L	
operating class of the fuse link		gR	
type of voltage of the operating voltage		DC	
Supply voltage			
supply voltage		900 V	
• at DC			
Breaking Capacity			
switching capacity current		100 kA	
• at DC according to IEC 60947-2 rated value			
Dissipation			
power loss [W]		68 W	
power loss [W]		68 W	
• for rated value of the current at AC in hot operating state per pole			
• maximum		68 W	
Product details			
product description		with blade contacts, silver-plated	
accessories included		no	
Mechanical Design			
mounting position		Any, preferably vertical	
Environmental conditions			
ambient temperature during operation		50 °C	
• minimum			
• maximum		20 °C	
environmental category		-20 to +50 at 95% relative humidity	
Approvals Certificates			
General Product Approval		other	Environment



EG-Konf.



[Confirmation](#)

[Miscellaneous](#)



Environment

[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NB1234-3KK20>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NB1234-3KK20>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NB1234-3KK20

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/4/2025 

