

Product data sheet

Specifications



Repacked, remote indication auxiliary, Acti9 iACTs, 1 NO + 1 NC

A9C15914W



This repacked option saves 0.178 over the standard condition

Main

Range of product	ICT
Range	Acti9
Device short name	iACTs
Product or component type	Remote indication auxiliary
Signal contacts composition	1 NO + 1 NC

Complementary

Signalling circuit voltage	24 V AC/DC: 10 mA 230 V AC: 50/60 Hz 5 A 230 V AC: 50/60 Hz 2 A 130 V DC: 1 A
[Uc] control circuit voltage	24...240 V AC 50/60 Hz 24...130 V DC
Range compatibility	Acti9 iCT
[Ui] rated insulation voltage	440 V
[Uimp] rated impulse withstand voltage	4 kV
Mounting mode	Fixed, on the right of CT
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	1
Height	81 mm
Width	9 mm
Depth	68 mm
Colour	White
Auxiliary connection terminal	Tunnel type terminals 2 cable(s) flexible 2.5 mm ² Tunnel type terminals 2 cable(s) rigid 1.5 mm ² Tunnel type terminals 1 cable(s) rigid 1.5...2.5 mm ² Tunnel type terminals 1 cable(s) flexible 1.5...2.5 mm ²
Wire stripping length	9 mm
Tightening torque	0.8 N.m
Product compatibility	ICT
Market segment	Small commercial Residential
Compatibility code	IACTs

Environment

Standards	EN 60947-5
-----------	------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

IP degree of protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	7.000 cm
Package 1 Length	8.500 cm
Package 1 Weight	37.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	928.000 g

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.2 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

429095ee-388a-4184-bea4-16f87e374975

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Offer Marketing Illustration

Product benefits / Features

Technical Benefits
Acti9 ICT

