

T9GV5L14-110

 DO NOT USE FOR NEW DESIGN

TE Internal #: 1558660-9

TE Internal Description: T9GV5L14-110

PCB Power Relay: 30 amp, Monostable DC

[View on TE.com >](#)



All PCB Power Relay: 30 amp, Monostable DC (60)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1558660-9
[T9GV5L14-110WG](#)

TE Part # 1-1558665-9
[T9GS5L14-110WG](#)

TE Part # 1558665-9
[T9GS5L14-110](#)

Customers Also Bought

TE Part #T2040104101-000
[HE-010-MC](#)

TE Part #5747467-4
[HD-20 PLUG 9P RA 590 THD INS](#)

TE Part #CAT-C339-T419
[Power Resistor: Aluminum Housed, 75 Watt](#)

TE Part #1676914-7
[YR1 0.1% 374R](#)

TE Part #2-2176414-4
[7W STD M/OX 5% 180R](#)

TE Part #7-2176400-9
[3540 1K8 1%](#)

TE Part #7-1676915-7
[YR1 0.1% 137R](#)

TE Part #6-2176245-4
[CRGS1206 5% 180K](#)

TE Part #4-2176245-7
[CRGS1206 5% 6K8](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1558660-9_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1558660-9_B.3d_igs.zip](#)

English



Customer View Model

[ENG_CVM_CVM_1558660-9_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[PB 30A PCB Relay T9G Series](#)

English

[T9G Data Sheet](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English

Agency Approvals

[VDE Certificate](#)

English