

Product data sheet

Automation technology - Data transmission




Product description	M12 Lead-through for control cabinet, Contacts: 4, shielded, pluggable, IP67, UL 2238, Rear mounting
Area	M12-D
Coding	D-coded
Series	825
Part no.	09 5246 00 04


Illustration



Scale drawing



Contact arrangement (Plug-in side)



You can find the assembly instructions on the next page.

Technical data

General features

Part no.	09 5246 00 04
Connector design	Lead-through for control cabinet
Type standard	DIN EN 61076-2-101
Coding	D-coded
Version	Lead-through for control cabinets
Connector locking system	screw
Termination	pluggable
Degree of protection	IP67
Temperature range from/to	-40 °C / 85 °C
Mechanical operation	> 100 Mating cycles
Weight (g)	62.30
Customs tariff number	85369010
Country of Origin	DE

Electrical parameters

Rated voltage	250 V
Rated impulse voltage	2500 V
Rated current	4.0 A
Insulation resistance	> 10 ⁸ Ω
Pollution degree	3
Transmission rate	CAT 5
Overvoltage category	II
Insulating material group	II
EMC compliance	shielded
Shield connection	Shield on the housing

Product data sheet

Automation technology - Data transmission



Product description	M12 Lead-through for control cabinet, Contacts: 4, shielded, pluggable, IP67, UL 2238, Rear mounting
Area	M12-D
Coding	D-coded
Series	825
Part no.	09 5246 00 04

Material

Contact body material	PA
Contact material	CuZn (brass)
Contact plating	Au (gold)
Locking material	Zinc die-cast nickel-plated
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	5bf177f5-454f-42e0-baae-c2096fd479a4

Authorization/approvals

Approvals	UL 2238
-----------	---------

Classifications



eCl@ss 11.1	27-44-01-09
ETIM 9.0	EC003569

Declarations of conformity

Low Voltage Directive	2014/35/EU (EN 60529:1991 2014/35/EU;EN 60204-1:2018)
-----------------------	---

Assembly instructions / Panel cut-out

Schaltschrankdurchführung mit Durchgangsbohrung
Lead-through for control cabinet with bore hole



Anzugsdrehmoment/Tightening moment
1-1,2 Nm

Product data sheet

Automation technology - Data transmission



Product description	M12 Lead-through for control cabinet, Contacts: 4, shielded, pluggable, IP67, UL 2238, Rear mounting
Area	M12-D
Coding	D-coded
Series	825
Part no.	09 5246 00 04

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).