

## solenoid valve VUVG-B18-T32C-AZT-F-1T1L Part number: 8004885

## **FESTO**





## Data sheet

Feature	Value
Valve function	2x3/2 closed, monostable
Type of actuation	electrical
Valve size	18 mm
Standard nominal flow rate	800 l/min
Operating pressure	1.5 10 bar
Design structure	Piston slide
Type of reset	Air spring
Protection class	IP65
	IP67
Authorisation	c CSA us (OL)
	c UL us - Recognized (OL)
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Manual override	detenting
	Pushing
Type of piloting	Piloted
Pilot air supply	external
Signal status display	LED
Pilot pressure	1.5 8 bar
Max. switching frequency	3 Hz
Switching time off	34 ms
Switching time on	15 ms
Duty cycle	100%
Max. positive test pulse with logic 0	1,600 µs
Max. negative test pulse with logic 1	3,000 µs
Characteristic coil data	22 V DC: 1 W
Permissible voltage fluctuation	+/- 10 %
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further
	operation)
Vibration resistance	Transport application test at severity level 2 in accordance with FN
	942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Medium temperature	-5 60 °C
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Ambient temperature	-5 60 °C
Product weight	145 g
Electrical connection	via manifold block
Mounting type	on manifold rail
Materials note	Conforms to RoHS
Material seals	HNBR
	NBR
Material housing	Wrought Aluminium alloy