



Automotive Parts > Automotive Connectors > Automotive Housings



Connector & Housing Type: **Housing for Female Terminals**

Number of Positions: 2

Sealable: **Yes**

Operating Temperature Range: **-40 – 85 °C [ -40 – 185 °F ]**

Number of Rows: 1

## Features

### Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	Integrated in Housing
Connector System	Wire-to-Panel
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	2
Number of Rows	1

### Electrical Characteristics

Operating Voltage	25 VDC
-------------------	--------

### Body Features

Cable Exit Angle	180°
------------------	------



Primary Product Color	Black
-----------------------	-------

### Contact Features

Contact Size	5mm
Contact Type	Socket
Mating Pin Diameter	4.98 mm[.196 in]
Contact Current Rating (Max)	25 A

### Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Polarization
Mating Alignment	With
Connector Mounting Type	Panel Mount

### Housing Features

Housing Material	PA GF
Centerline (Pitch)	10 mm[.4 in]

### Dimensions

Product Width	53.4 mm[2.1 in]
Product Length	62 mm[2.44 in]
Connector Height	56.1 mm[2.2 in]

### Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
Operating Temperature (Max)	85 °C[185 °F]

### Operation/Application

Circuit Application	Power
---------------------	-------

### Industry Standards

IP Rating	IP68
UL Flammability Rating	UL 94HB

### Packaging Features

Packaging Quantity	200
Packaging Method	Box

### Other



Serviceable	No
Connector Position Assurance Capable	No

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

### Compatible Parts



### Also in the Series | Round Connector System




Automotive Housings(30)



Automotive Seals & Cavity Plugs(4)



Automotive Signal & Power Connector Housings(12)



Other Automotive Connector Accessories(31)

## Customers Also Bought



TE Part #3876656003  
LSTT-R-4.8-0



TE Part #DTM12P-DC  
PROTECT CVR, 12P, REC, GRY, DTM



TE Part #DTM06-12SB-E003  
PLG, 12P, BLK, N, CAP, B



TE Part #T4111001051-000  
M12,MALE,STRAIGHT,A CODE,5P, PG7,GOLD




TE Part #206705-4  
CPC RECPT ASSEMBLY SIZE 13-9



TE Part #927231-3  
HONHUS UMNL V0 9-P



TE Part #1241380-3  
AMP MCP 1.5K, CONTACT, SWS



TE Part #4-1437290-0  
34POS,SUPERSEAL,REC HSG ASSY, SLD,COD 1



TE Part #3-1447221-3  
S/S REC CONTACT ASSY, AU, 0.75-1.25



TE Part #1-2329360-7  
PB OFF/ON RC RED M4 TERM. IP68

## Documents

### Product Drawings

[CAR RECPT DIN9680 2way](#)

English

### CAD Files

[3D PDF](#)

3D

### Customer View Model

[ENG\\_CVM\\_CVM\\_CAR2SC00\\_C.2d\\_dxf.zip](#)



English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_CAR2SC00\\_C.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_CAR2SC00\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Product Specifications**

[Product Specification](#)

English