



Image may differ from product. See technical specification for details.

TMBA G11H

SKF Heat and Oil Resistant Gloves TMBA G11H

The SKF heat and oil resistant gloves TMBA G11H are specially designed for the handling of hot and oily bearings. They are made of multiple layers of different kinds of fabric to obtain an unique combination of heat, cut, oil and water resistance.

- Melt and burn proof KEVLAR® gloves
- Remains heat resistant when wet
- Cut resistant
- Suitable for brief sub-merging in liquids of a temperature up to 120 °C (248 °F), e.g. hot oil bath
- Tested and certified for mechanical hazards (EN 388) and thermal hazards (EN 407)

Overview

Dimensions

Suitable for Hand size	10
------------------------	----

Performance

Use temperature (max.)	250 °C
Performance according EN 420: General requirements	Sizes 10
Performance according EN 388: Mechanical risks	Abrasion resistance: 4 Cut resistance (Coup): 5 Tear resistance: 4 Puncture resistance: 3 Cut resistance (TDM): D
Performance according EN 407: Thermal risks	Limited Flame Spread: 4 Contact heat: 3 Convective heat: 4 Radiant heat: 2 Small drops of molten metal: X Large drops of molten metal: X Removal of Gloves: Pass

Properties

Recommended applications	Heat resistant gloves specially designed for the handling of hot and oily bearings
Oil and grease resistant	Yes
Suitable for submerging in liquids	Yes, max. 120°C
Material, outer layer	Para-aramid
Material, middle layer	Nitrile
Material, inner layer	Cotton
Special features	Non-allergenic
Washing	Not recommended
Colour	Yellow
Recommended storage temperature	5.0 – 25.0 °C
Content	1 pair

Logistics

Product net weight	0.32 kg
eClass code	23-05-19-01
UNSPSC code	40101831

Compatible products

Recommended product

SKF Extreme Temperature Gloves TMBA G11ET

[TMBA G11ET](#)

Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.