

V23079B1206B301

✓ ACTIVE

TE Internal #: 3-1393788-9

TE Internal Description: V23079B1206B301

Small Signal Relay, Axicom P2 Standard

[View on TE.com >](#)



[All Small Signal Relay, Axicom P2 Standard \(23\)](#)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1393789-9

V23079E1206B301

Customers Also Bought

TE Part #5161390-1

01P.DIP SWITCH ASSY

TE Part #1-1586037-0

10P VERT HDR VAL-U-LOK V2

TE Part #2-1586037-0

20P VERT HDR VAL-U-LOK V2

TE Part #5161390-2

02P.DIP SWITCH ASSY

TE Part #4-794630-2

12P MICRO MNL ASSY,VRT,HDR,LF

TE Part #1-1586037-2

12P VERT HDR VAL-U-LOK V2

TE Part #1-1586037-4

14P VERT HDR VAL-U-LOK V2

TE Part #350431-1

06P UMNL PIN HDR ASSY V2 NAT

TE Part #1586037-8

8P VERT HDR VAL-U-LOK V2

TE Part #1-1586037-6

16P VERT HDR VAL-U-LOK V2

Documents

Product Drawings

V23079B1206B301

English

V23079B1206B301

English

CAD Files



Customer View Model

[ENG_CVM_CVM_1393788-5_A.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1393788-5_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1393788-5_A.3d_stp.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-1393788-9_E1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1393788-9_E1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1393788-9_E1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Transportation, Storage, Handling, Assembly and Testing of Axicom Through Hole Terminal \(THT\) Relays](#)

English

[Transportation, Storage, Handling, Assembly and Testing of AXICOM THT Relays](#)

English

[AXICOM Latching Relays](#)

English

[P2 Relay Datasheet](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English

Agency Approvals

[UL](#)

English