

Product datasheet

Specifications



Acti9 IHP 1C w (24h/7d) programmable time switch

Local distributor code:

408113997

CCT15441

EAN Code: 3606489524456

Main

range of product	Acti9
product name	Acti9 IHP
Device short name	IHP
Product or component type	Programmable digital time switch
Device application	Building
Number of channels	1
User language	English French German Dutch Italian Spanish Portuguese Danish Norwegian Swedish Finnish

Complementary

Load type	incandescent lamp: 2600 W halogen lamp: 2600 W non-corrected fluorescent tube: 2600 VA serial-compensated fluorescent tube: 2600 VA parallel compensated fluorescent lamp: 400 VA (48 µF) compact fluorescent lamp: 400 W < 2 W LED lamp: 25 W > 2 W LED lamp: 200 W
Maximum power consumption in W	0.5 W standby
Maximum switching current	10 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
Minimum switching current	10 mA 230 V AC 100 mA 24 V AC/DC
[Ue] rated operational voltage	230 V AC +10 % -15 % at 50/60 Hz
Electrical insulation class	Class II
Output type	Dry contact
Accuracy	+/- 0.25 s/day 25 °C
contacts type	C/O
Cycle duration	24 hours + 7 days
Maximum number of switchings	56
Minimum interval duration	1 min

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Function available	Code lock function Holiday schedules Automatic winter/summer time changeover On/off permanent switching Manual operation On/off switching times Switch preselection
control button type	4 push-buttons
Backup time	10 years time and program saving
Type of setting	Weekly programming
Connections - terminals	2 x 0.5...2.5 mm² screw terminals solid or flexible 1 x 2.5 mm² screw terminals solid or flexible with sleeve
Mounting support	TH35 DIN rail conforming to EN 60715
Width	45 mm
Height	92.6 mm
Depth	66.7 mm
Product weight	114 g
Marking	CE
Overvoltage category	Class 3
Function	None
Absence for holidays	Yes
Time changeover	Automatic
Updated by	None

Environment

Standards	EN 60730-2-7:2010
Ambient air temperature for operation	-30...55 °C
ambient air temp for storage/ transportation	-30...70 °C
Relative humidity	90 %, non-condensing
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.800 cm
Package 1 Width	6.500 cm
Package 1 Length	10.300 cm
Package 1 Weight	159.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	40
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.785 kg

Unit Type of Package 3	P12
Number of Units in Package 3	320
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	66.500 kg

Logistical informations

Country of origin	DE
-------------------	----


Contractual warranty

Warranty	18 months
----------	-----------


Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)


[How we assess product sustainability >](#)

<div>Environmental footprint</div>	
Environmental Disclosure	Product Environmental Profile

Use Better

<div>Materials and Substances</div>	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	5c23d91a-4c63-483e-b70a-45310671b035
REACH Regulation	REACH Declaration

Use Again

<div>Repack and remanufacture</div>	
Removable battery	No
Take-back	No