

RNF-100-1-1/2-4-STK

✓ ACTIVE

Raychem | Raychem RNF-100

TE Internal #: 5053362025

Raychem RNF-100, Heat Shrink Tubing, Yellow, Single Wall Type,
38.1 Expanded Inside Diameter (Min) 1.5 Expanded Inside
Diameter (Min)

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Yellow**

Wall Type: **Single**

Expanded Inside Diameter (Min): **38.1 mm [1.5 in]**

Recovered Inside Diameter (Max): **19.1 mm [.75 in]**

Shrink Ratio: **2:1**

Features

Product Type Features

Product Family	RNF-100
Wall Type	Single

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Yellow
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	.4 mm[.016 in]
Cut Length	1220 mm[48.031 in]
Recovered Wall Thickness (Nominal)	1 mm[.039 in]
Expanded Inside Diameter (Min)	38.1 mm[1.5 in]
Recovered Inside Diameter (Max)	19.1 mm[.75 in]
Heat Shrink Tubing Size Range	19.1 – 38.1 mm[.75 – 1.5 in]



Usage Conditions

Fluid Resistance	Splash Protection
Shrink Temperature (Min)	95 °C
Heat Shrink Tubing Flammability	Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Heat Shrink Tubing Resistance	Abrasion, Fluids, Mechanical Damage, Strain
Recovery Temperature	121 °C

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Stick
------------------	-------

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

RNF-100-1-1/2-4-STK

Raychem RNF-100, Heat Shrink Tubing, Yellow, Single Wall Type, 38.1 Expanded Inside Diameter (Min) 1.5 Expanded Inside Diameter (Min)



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | Raychem RNF-100



Heat Shrink Tubing(730)



Power Cable Tubing & Accessories(49)

Customers Also Bought



TE Part #130114
PIDG RING TONGUE



TE Part #5053352014
RNF-100-1-1/2-2-STK




TE Part #1-1337406-0
N Str Jk PS 50Ohm Silver Pltd PSF 1 /4M,



TE Part #5053372012
RNF-100-1-1/2-6-STK



TE Part #5053312037
RNF-100-1-4-STK



TE Part #2820093010
44A0111-16-9



TE Part #710031-6
XCT 10-8



TE Part #710031-8
XCT 10-10



TE Part #9360713001
99M0111-20-2



TE Part #710030-7
XCT 16-10

Documents

Product Drawings

RNF-100-1-1/2-4-STK

English

Datasheets & Catalog Pages

RNF-100 Pages from 9-1773447-9

English

Application Tooling for Raychem Heat Shrink Product

English

Flexible, Flame-Retardant, High Performance, Polyolefin Heat-Shrinkable Tubing

English

Product Specifications

Product Specification

English

Global Dimensional Life for RAYCHEM Heat Shrink Tubing Standard Size Products (Customer Distribution)

English