



Professional LED hybrid construction floodlight CL 5050 MBAH, 6800 lm, IP65

Work spotlight with clamping device can be attached anywhere and optimally aligned for use thanks to the ball joint.



**ENGINEERED IN
GERMANY**



3 YEARS
MANUFACTURER
GUARANTEE



Product number 1173070030
EAN 4007123684731

DESCRIPTION

- Ideally suited for assembly work, in cellars and on workbenches.
- Work spotlight with special clamping device (max. 82 mm) for easy installation by clamping to work surfaces, pipes, panels, etc.
- More flexibility thanks to hybrid technology: battery and mains operation possible, automatic switchover from mains to battery in the event of a power failure.
- With 5 m detachable cable (H05RN-F 2X1.0).
- Break-proof and impact-resistant plastic/aluminium housing with strong, sturdy clip.
- Easy alignment of the work light thanks to ball bearing, the angle of inclination of the work light can be flexibly adjusted.
- With ball joint for individual alignment in all directions by almost 360 degrees.
- With 4 switching levels (100 % - 75 % - 50 % - 25 %).
- Bluetooth control via the free BT-Control app from Brennenstuhl.
- Functions include switching on and off, brightness setting, grouping (several spotlights can be controlled simultaneously) and automatic switch-off via a timer.
- Integrated USB C power bank for charging smartphones etc.
- Li-Ion battery 7.4 V/6.6 Ah with charge indicator.
- Category 2 equipment (K2 DGUV 203-005): Use for rough operation with high mechanical, physical and chemical impacts.

Professional LED hybrid construction floodlight CL 5050 MBAH, 6800 lm, IP65

Work spotlight with clamping device can be attached anywhere and optimally aligned for use thanks to the ball joint.



Product number 1173070030
EAN 4007123684731

TECHNICAL DATA

Luminous flux	6800 lm	Battery charging time approx.	2.5 h
Power consumption	50 W	Number of batteries	1
Colour temperature	6500 K	Battery type	Battery pack
Min.-Max. Nominal input voltage	100 V - 240 V	Battery technology	Lithium-ion
Cable length	5 m	Impact strength	IK08
Cable designation	H05RN-F 2X1,0	Protection class	II
Battery capacity	6.6 Ah	Degree of protection (IP)	IP65
Battery voltage	7.4 V	Colour	black/grey
Light duration max.	12 h		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	3.33 kg
Weight of product (without packaging)	2.99 kg	Dimension LxWxH (incl. packing)	13 cm x 19 cm x 29.5 cm
Dimension LxWxH (without packing)	18 cm x 11 cm x 28.6 cm		

SCOPE OF DELIVERY

LED hybrid site floodlight CL 5050 MBAH, 5m cable F2X1.0, power supply unit