

FEATURES

- **Heavy Duty Design:** Supports a tensile strength of 80 kg, ideal for securing large bundles.
- **UV Resistant:** Suitable for outdoor use, providing long-lasting performance.
- **Wide Temperature Range:** Operates effectively up to 85 °C, accommodating various environments.
- **Large Bundle Capacity:** Accommodates a maximum bundle diameter of 372 mm, perfect for extensive cable management.
- **Nylon Material:** Offers durability and flexibility, ensuring secure fastening.
- **Fire Behaviour UL 94 V-2:** Provides a level of flame retardancy for safety.

RS PRO Heavy Duty Cable Tie, 1219 mm Nylon

RS Stock No: 656-071



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO heavy duty cable tie is designed for securing and organising large bundles of cables or wires. With a length of 1219 mm and made from durable nylon, it offers a reliable solution for managing complex cable systems in industrial environments. Its UV resistance ensures longevity even in outdoor applications.

General Specifications

| | |
|------------------|----------------------|
| Colour | Black |
| Product Type | Cable Tie |
| Sub Type | Heavy Duty Cable Tie |
| Tensile Strength | 80 kg |

Protection Category

| | |
|----------------|-----------|
| Fire Behaviour | UL 94 V-2 |
| UV Resistant | Yes |

Mechanical Specifications

| | |
|-------------------------|---------|
| Length | 1219 mm |
| Material | Nylon |
| Maximum Bundle Diameter | 372 mm |
| Width | 9 mm |

Operation Environment Specifications

| | |
|-------------------------------|-------|
| Maximum Operating Temperature | 85 °C |
|-------------------------------|-------|

Approvals

| | |
|---------------------|---|
| Standards/Approvals | ABS 15-TA1338482-PDA, CE 40022513, cULus E97527, DNV TAE00000US, LR 16-80006, RoHS, UL94V-2, VDE 40022513 |
|---------------------|---|