



### Main

Range of product	Canalis
Range compatibility	KT busbar trunking KS busbar trunking
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KS busbar trunkingplug-in Canalis KT busbar trunking with KS type plug-in
[Ie] rated operational current	400 A at 35 °C
Protection type	fuse isolator: for aM blade type fuse, size 2 - 400 A conforming to NF fuse isolator: for gG blade type fuse, size 2 - 400 A conforming to NF
Provided equipment	fuse to be ordered separately
Mounting mode	Plug-in with fixed polarity
Tap-off unit polarity	3L+PEN
Colour	White (RAL 9001)

### Complementary

Device application	Medium power distribution
[Ue] rated operational voltage	230...690 V depending on protective device
[Uimp] rated impulse withstand voltage	6.8 kV
[Ui] rated insulation voltage	500 V depending on protective device
Network frequency	50/60 Hz
Electrical connection	Copper cable lug - ISO50 240 mm <sup>2</sup> flexible Copper cable lug - ISO50 240 mm <sup>2</sup> rigid
Door/Cover opening side	Right
Tap-off unit disconnection mode	By opening the door
Standards	IEC 61439-1 IEC 61439-6
Body material	Metal
Width	600 mm
Depth	316 mm

Depth (door open)	855 mm
Height	600 mm
Net weight	29.2 kg

## Environment

Earthing system	TN-C
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------

