



**Part Number :** [702871001](#)

**Product Description :** 2.54mm Pitch C-Grid Header, Breakaway, Dual Row, Vertical, with Retention Pin, 6 Circuits, 6.10mm Mating Pin Length, Tin (Sn) Plating

**Series Number :** 70287

**Status :** Active

**Product Category :** PCB Headers and Receptacles



---

## Documents & Resources

### Drawings

[702871001\\_sd.pdf](#)

[PK-70873-0353-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[713080001-AS-000.pdf](#)

[PS-70280-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Compliant with Exemption 44; 33   |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)4165-DC (25 June 2025)   |
| EU RoHS            | Compliant per EU 2015/863   |

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

|                |   |
|----------------|---|
| Status         | Active  |
| Category       | PCB Headers and Receptacles   |
| Series         | 70287   |
| Description    | 2.54mm Pitch C-Grid Header, Breakaway, Dual Row, Vertical, with Retention Pin, 6 Circuits, 6.10mm Mating Pin Length, Tin (Sn) Plating |
| Application    | Board-to-Board, Signal, Wire-to-Board   |
| Component Type | PCB Header  |
| Product Name   | C-Grid  |
| UPC            | 822350865548  |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Electrical

|                               |         |
|-------------------------------|---------|
| Current - Maximum per Contact | 3.0A    |
| Voltage - Maximum             | 250V DC |

### Physical

|                                |                                |
|--------------------------------|--------------------------------|
| Breakaway                      | Yes                            |
| Circuits (Loaded)              | 6                              |
| Circuits (maximum)             | 6                              |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 25                             |
| First Mate / Last Break        | No                             |
| Flammability                   | 94V-0                          |
| Glow-Wire Capable              | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | N/A                            |
| Lock to Mating Part            | None                           |
| Material - Metal               | Brass                          |
| Material - Plating Mating      | Tin                            |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 0.382/g                        |
| Number of Rows                 | 2                              |
| Orientation                    | Vertical                       |
| Packaging Type                 | Bag                            |
| PCB Locator                    | No                             |
| PCB Retention                  | None                           |
| PCB Thickness - Recommended    | 1.57mm                         |
| PC Tail Length                 | 3.18mm                         |
| Pitch - Mating Interface       | 2.54mm                         |
| Pitch - Termination Interface  | 2.54mm                         |
| Plating min - Mating           | 3.810µm                        |
| Plating min - Termination      | 3.810µm                        |
| Polarized to Mating Part       | No                             |
| Polarized to PCB               | No                             |
| Shrouded                       | No                             |
| Stackable                      | Yes                            |
| Temperature Range - Operating  | -40° to +120°C                 |
| Termination Interface Style    | Through Hole                   |

## Solder Process Data

|                              |      |
|------------------------------|------|
| Max-Duration                 | 5    |
| Lead-Free Process Capability | WAVE |
| Max-Cycle                    | 1    |
| Max-Temp                     | 245  |

---

## Mates With / Use With

### Mates with Part(s)

| Description   | Part Number  |
|---|--------------|
| C-Grid Right-Angle, Dual Row, Surface Mount PCB Receptacles           | <u>71979</u> |
| C-Grid Vertical, Dual Row, High Profile, Surface Mount PCB Connectors | <u>71395</u> |
| C-Grid Vertical, Dual Row, High Profile, Through Hole PCB Receptacles | <u>71850</u> |
| 2.54mm Pitch C-Grid Shunt Terminal Housings                           | <u>7859</u>  |