


TE Internal #: 447192-4  
PCB Mount Receptacle, Vertical, Board-to-Board, 150 Position, 2.54 mm [.1 in] Centerline, Gold (Au), Through Hole - Solder, Signal, Brown, Package

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**  
PCB Mount Orientation: **Vertical**  
Connector System: **Board-to-Board**  
Number of Positions: **150**  
Number of Rows: **3**

Features

Product Type Features

PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	50
Number of Loaded Positions	150
Board-to-Board Configuration	Perpendicular
Stackable	No
PCB Mount Orientation	Vertical
Number of Positions	150
Number of Rows	3

Body Features

Primary Product Color	Brown
-----------------------	-------

Contact Features

Contact Mating Area Plating Material Thickness	1.27 µm[50 µin]
Mating Square Post Dimension	.64 mm[.025 in]



	150 µin
Contact Layout	Matrix
Contact Base Material	Beryllium Copper
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Socket
Contact Current Rating (Max)	3 A

Termination Features

Rectangular Termination Post & Tail Width	1.12 mm[.044 in]
Rectangular Termination Post & Tail Thickness	.81 mm[.032 in]
Termination Post & Tail Length	5.84 mm[.23 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Alignment Type	Polarized
PCB Mount Retention Type	Mounting Hole
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Polyphenylene Sulfide (PPS)
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Stack Height	15.24 mm[.6 in]
Connector Width	12.44 mm[.49 in]
PCB Thickness (Recommended)	2.44 mm[.096 in]
Connector Height	11.43 mm[.45 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Solder Process Feature	Board Standoff
------------------------	----------------



Circuit Application	Signal
Industry Standards	
UL Flammability Rating	UL 94V-0

Packaging Features	
Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not lead free process capable


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Customers Also Bought



Documents

Product Drawings

3 ROW BOX RECP 150 POS 100 C/L

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_447192-4\_C\_c-447192-4-c.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_447192-4\_C\_c-447192-4-c.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_447192-4\_C\_c-447192-4-c.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

447192-4

PCB Mount Receptacle, Vertical, Board-to-Board, 150 Position, 2.54 mm [.1 in]  
Centerline, Gold (Au), Through Hole - Solder, Signal, Brown, Package



Product Specifications

Application Specification

English