

KEMET Part Number: PME271M522MR30
(P276QL223M275A)

PME271M/P276, Film, Metallized Paper, Safety, 0.022 uF, 20%, 275 VAC (X2), 630 VDC, 110°C, Lead Spacing = 15.2mm



Dimensions	
L	18.5mm MAX
H	12.5mm MAX
T	6mm MAX
S	15.2mm +/-0.4mm
LL	30mm +5mm
F	0.8mm NOM

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	400

General Information	
Supplier:	KEMET
Series:	PME271M/P276
Dielectric:	Metallized Paper
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
AEC-Q200:	No
Construction:	Molded
Miscellaneous:	SRF= 10 MHz

Specifications	
Capacitance:	0.022 uF
Capacitance Tolerance:	20%
Voltage AC:	275 VAC (X2)
Voltage DC:	630 VDC
Temperature Range:	-40/+110°C
Rated Temperature:	110°C
Dissipation Factor:	1.30% 1kHz
Insulation Resistance:	12 GOhms
Max dV/dt:	1200 V/us
Safety Class:	X2