SIEMENS

Data sheet

6ES7211-1BE40-0XB0

SIMATIC S7-1200, CPU 1211C, compact CPU, AC/DC/relay, onboard I/O: 6 DI 24 V DC; 4 DO relay 2A; 2 AI 0-10 V DC, Power supply: AC 85-264 V AC at 47-63 Hz, Program/data memory 50 KB



General information	
Product type designation	CPU 1211C AC/DC/relay
Firmware version	V4.2
Engineering with	
 Programming package 	STEP 7 V14 or higher
Supply voltage	
Rated value (AC)	
• 120 V AC	Yes
• 230 V AC	Yes
permissible range, lower limit (AC)	85 V
permissible range, upper limit (AC)	264 V
Line frequency	
 permissible range, lower limit 	47 Hz
• permissible range, upper limit	63 Hz
Input current	
Current consumption (rated value)	60 mA at 120 V AC; 30 mA at 240 V AC
Current consumption, max.	180 mA at 120 V AC; 90 mA at 240 V AC
Inrush current, max.	20 A; at 264 V

l²t	0.8 A ² ·s
Output current	
for backplane bus (5 V DC), max.	750 mA; Max. 5 V DC for CM
·····	
Encoder supply	
24 V encoder supply	
• 24 V	20.4 to 28.8V
Power loss	
Power loss, typ.	10 W
Memory	
Work memory	
● integrated	50 kbyte
• expandable	No
Load memory	
● integrated	1 Mbyte
 Plug-in (SIMATIC Memory Card), max. 	with SIMATIC memory card
Backup	
• present	Yes
• maintenance-free	Yes
• without battery	Yes
CPU processing times	
for bit operations, typ.	0.08 µs; / instruction
for word operations, typ.	1.7 μs; / instruction
for floating point arithmetic, typ.	2.3 μs; / instruction
CPU-blocks	
Number of blocks (total)	DBs, FCs, FBs, counters and timers. The maximum number of addressable blocks ranges from 1 to 65535. There is no
	restriction, the entire working memory can be used
OB	
• Number, max.	Limited only by RAM for code
Data areas and their retartivity	
Data areas and their retentivity Retentive data area (incl. timers, counters, flags),	10 kbyte
max.	
Flag	
• Number, max.	4 kbyte; Size of bit memory address area
Local data	
 per priority class, max. 	16 kbyte; Priority class 1 (program cycle): 16 KB, priority class 2
	to 26: 6 KB
Address area	
Process image	
 Inputs, adjustable 	1 kbyte

Outputs, adjustable	1 kbyte
Hardware configuration	
Number of modules per system, max.	3 communication modules, 1 signal board
Time of day	
Clock	
 Hardware clock (real-time) 	Yes
Backup time	480 h; Typical
 Deviation per day, max. 	±60 s/month at 25 °C
Digital inputs	
Number of digital inputs	6; Integrated
 of which inputs usable for technological functions 	3; HSC (High Speed Counting)
Source/sink input	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	6
Input voltage	
Rated value (DC)	24 V
• for signal "0"	5 V DC at 1 mA
● for signal "1"	15 V DC at 2.5 mA
Input current	
● for signal "1", typ.	4 mA; nominal
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four
— at "0" to "1", min.	0.2 ms
— at "0" to "1", max.	12.8 ms
for interrupt inputs	
— parameterizable	Yes
for counter/technological functions	
— parameterizable	Single phase : 3 @ 100 kHz, differential: 3 @ 80 kHz
Cable length	
• shielded, max.	500 m; 50 m for technological functions
• unshielded, max.	300 m; For technological functions: No
Digital outputs	
Number of digital outputs	4; Relays
Switching capacity of the outputs	
• with resistive load, max.	2 A
• on lamp load, max.	30 W with DC, 200 W with AC
Output delay with resistive load	

• "0" to "1", max.	10 ms; max.
• "1" to "0", max.	10 ms; max.
Relay outputs	
 Number of operating cycles, max. 	mechanically 10 million, at rated load voltage 100 000
Cable length	
• shielded, max.	500 m
• unshielded, max.	150 m
Analog inputs Number of analog inputs	2
Input ranges	2
Voltage	Yes
•	
Input ranges (rated values), voltages	Vee
• 0 to +10 V	Yes
Input resistance (0 to 10 V)	≥100k ohms
Cable length	
 shielded, max. 	100 m; twisted and shielded
Analog outputs	
Number of analog outputs	0
Analog value generation for the inputs	
Integration and conversion time/resolution per channel	10 bit
 Resolution with overrange (bit including sign), max. 	TO DIL
	Yes
Integration time, parameterizable	625 µs
Conversion time (per channel)	020 µ9
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
1 Interface	
1. Interface Interface type	PROFINET
Physics	Ethernet
Isolated	Yes
automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
Interface types	
Number of ports	1
integrated switch	No
_	
	Yes
PROFINET IO ControllerPROFINET IO Device	1 00
	Yes

SIMATIC communication	Yes
Open IE communication	Yes
• Web server	Yes
Media redundancy	No
PROFINET IO Controller	
 Transmission rate, max. 	100 Mbit/s
Services	
— PG/OP communication	Yes
— S7 routing	Yes
— Isochronous mode	No
— Open IE communication	Yes
— IRT	No
— MRP	No
— MRPD	No
— PROFlenergy	No
— Prioritized startup	Yes
 — Number of IO devices with prioritized 	16
startup, max.	
 Number of connectable IO Devices, max. 	16
 — Number of connectable IO Devices for RT, max. 	16
— of which in line, max.	16
— Activation/deactivation of IO Devices	Yes
 — Number of IO Devices that can be simultaneously activated/deactivated, max. 	8
— Updating time	The minimum value of the update time also depends on the communication component set for PROFINET IO, on the number

PROFINET IO Device

Services	
— PG/OP communication	Yes
— S7 routing	Yes
— Isochronous mode	No
— Open IE communication	Yes
— IRT	No
— MRP	No
— MRPD	No
— PROFlenergy	Yes
— Shared device	Yes
— Number of IO Controllers with shared	2
device, max.	

of IO devices and the quantity of configured user data.

Protocols

Supports protocol for PROFINET IO	Yes
PROFIBUS	Yes; CM 1243-5 required
AS-Interface	Yes; CM 1243-2 required
Protocols (Ethernet)	
• TCP/IP	Yes
• DHCP	No
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
Open IE communication	
• TCP/IP	Yes
— Data length, max.	8 kbyte
 — several passive connections per port, supported 	Yes
 ISO-on-TCP (RFC1006) 	Yes
— Data length, max.	8 kbyte
• UDP	Yes
— Data length, max.	1 472 byte
Web server	
 User-defined websites 	Yes
Further protocols	
• MODBUS	Yes
Communication functions	
S7 communication	
• supported	Yes
• as server	Yes
• as client	Yes
 User data per job, max. 	See online help (S7 communication, user data size)
Web server	
● supported	Yes
Number of connections	
• overall	16; dynamically
Test commissioning functions	
Status/control	
Status/control variable	Yes
Variables	Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters
Forcing	
• Forcing	Yes
Diagnostic buffer	
● present	Yes
Traces	

 Number of configurable Traces 	2
Memory size per trace, max.	512 kbyte
Interrupts/diagnostics/status information	
Diagnostics indication LED	
RUN/STOP LED	Yes
• ERROR LED	Yes
MAINT LED	Yes
Integrated Functions	
Number of counters	3
Counting frequency (counter) max.	100 kHz
Frequency measurement	Yes
controlled positioning	Yes
Number of position-controlled positioning axes, max.	8
Number of positioning axes via pulse-direction	Up to 4 with SB 1222
interface	
PID controller	Yes
Number of alarm inputs	4
Potential separation	
Potential separation digital inputs	
 Potential separation digital inputs 	500V AC for 1 minute
 between the channels, in groups of 	1
Potential separation digital outputs	
 Potential separation digital outputs 	Relays
 between the channels 	No
 between the channels, in groups of 	1
EMC	
Interference immunity against discharge of static electric	city
 Interference immunity against discharge of static electricity acc. to IEC 61000-4-2 	Yes
— Test voltage at air discharge	8 kV
— Test voltage at contact discharge	6 kV
Interference immunity to cable-borne interference	
 Interference immunity on supply lines acc. to IEC 61000-4-4 	Yes
 Interference immunity on signal cables acc. to IEC 61000-4-4 	Yes
Interference immunity against voltage surge	
● on the supply lines acc. to IEC 61000-4-5	Yes
Interference immunity against conducted variable disturbance induced by high-frequency fields	
 Interference immunity against high-frequency radiation acc. to IEC 61000-4-6 	Yes

Emission of radio interference acc. to EN 55 011	
 Limit class A, for use in industrial areas 	Yes; Group 1
• Limit class B, for use in residential areas	Yes; When appropriate measures are used to ensure compliance with the limits for Class B according to EN 55011
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
Marine approval	Yes
Ambient conditions	
Free fall	
 Fall height, max. 	0.3 m; five times, in product package
Ambient temperature during operation	
● min.	-20 °C
• max.	60 °C
 horizontal installation, min. 	-20 °C
 horizontal installation, max. 	60 °C
 vertical installation, min. 	-20 °C
 vertical installation, max. 	50 °C
Ambient temperature during storage/transportation	
● min.	-40 °C
● max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Operation, min.	795 hPa
• Operation, max.	1 080 hPa
• Storage/transport, min.	660 hPa
 Storage/transport, max. 	1 080 hPa
Altitude during operation relating to sea level	
 Installation altitude, min. 	-1 000 m
 Installation altitude, max. 	2 000 m
Relative humidity	
Operation, max.	95 %; no condensation
Vibrations	
 Vibration resistance during operation acc. to IEC 60068-2-6 	2 g (m/s²) wall mounting, 1 g (m/s²) DIN rail

 Operation, tested according to IEC 60068-2-6 	Yes
Shock testing	
• tested according to IEC 60068-2-27	Yes; IEC 68, Part 2-27 half-sine: strength of the shock 15 g (peak value), duration 11 ms
Pollutant concentrations	
 SO2 at RH < 60% without condensation 	S02: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60% condensation-free
Configuration	
Programming	
Programming language	
— LAD	Yes
— FBD	Yes
— SCL	Yes
Know-how protection	
 User program protection/password protection 	Yes
Copy protection	Yes
Block protection	Yes
Access protection	
 Protection level: Write protection 	Yes
 Protection level: Read/write protection 	Yes
 Protection level: Complete protection 	Yes
Cycle time monitoring	
• adjustable	Yes
Dimensions	
Width	90 mm
Height	100 mm
Depth	75 mm
Weights	
Weight, approx.	420 g
last modified:	04/13/2018