


Features

- Flexible and durable H05VVF3G1.5- pvc cable
- Unterminated end jacket stripped 25mm cores insulation stripped 5mm
- Moulded IEC -C19 Connector
- Fully moulded connectors for strength and durability
- Integrated strain relief for connection support and protection
- 2.5m Length

RS PRO 2.5m Power cable C19, IEC to Unterminated End 16 A 250 V

RS Stock No: 0857454



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- From RS PRO a high quality and durable power cord for connecting an appliance to a mains power supply. This power cord is supplied with 1.5mm sq. harmonised cable with unterminated end on one end and an IEC C19 (female) type connector on the end that connects to the appliance. The power lead features integrated strain relief that provide additional protection and support to the connector.

General Specifications

Connector A	C19, IEC Female – Straight EN60320 /C19
Connector B	Stripped end Outer jacket 25mm inner cores 5mm
Sheath Colour	Black
Material	PVC
Applications	IEC C19 were designed to be utilized in high power situations, such as Home Appliances, data centres, servers, network switches and uninterruptible power supplies (UPS) and professional food equipment.

Mechanical Specifications

Length	2.50m
--------	-------

Electrical Specifications

Power Cord Rating	16 A - 250V
Visual Inspection	100%
Electrical Test	100%
High pot test wire to wire	3k Vac for 2 sec.
Continuity test	25Aac to grounding / 20Aac to line and neutral
Polarity test	yes
Skin high pot test	6k Vac line to skin


Protection Category

Environmental Conformity	Eu-Directive 2002/96/EC (WEEE)
	Eu-Directive 2003/11/EC (Council Directive 76/769/EEC)
	Eu-Directive 2002/95/EC (RoHS-Compliant)

Approvals

C19 CONNECTOR	ENEC, CE
Stripped Ends	N/A
Cable	Harmonised <HAR>

2500 +/- 50



All Dimensions in mm