

### Features

- High performance design
- Performance Level 3
- RS232 standard interface
- Robust tin plated steel shell
- UL 94V-0 insulator
- Flanges containing 3.05 mm mounting holes for screw mounting to a panel

## RS PRO 50 WAY STRAIGHT CRIMP D-SUB CONNECTOR HOUSING, SOCKET

RS Stock No.: 0199102, 0199104



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

### Product Description

From RS PRO a high-performance D-Subminiature connector with a bright tin plated steel shell with grounding indents for EMI and RFI shielding. Crimp terminations on the rear of this connector allow the easy connection of wires. These D-sub connectors have an RS232 standard interface. The pins of this subminiature connector are of high quality and feature flanges with pre-drilled 3.05mm diameter holes on either side for easy panel mounting. These d-sub connectors are ideal for use in for I/O (input/output) interconnections in a wide range of industrial and commercial applications.

### General Specifications

<b>Number Of Contacts</b>	50
<b>Gender</b>	Female
<b>Body Orientation</b>	Straight
<b>Mounting Type</b>	Panel Mount
<b>D Connector</b>	Standard D-Sub
<b>D-Sub Shell Size</b>	D
<b>Termination Method</b>	Crimp
<b>Housing Material</b>	Steel
<b>Contact Material</b>	Copper Alloy
<b>Contact Plating</b>	Gold Over Nickel
<b>Application</b>	Computers, monitors and scanners, Networking and communications equipment; Data processing equipment, Industrial equipment, Test and measurement instrumentation, Remote Sensors and data loggers, Portable electric generation equipment
<b>Performance Level</b>	3
<b>Operating Temperature</b>	-55°C to 125°C

Material Flammability Rating	UL94 V-0
------------------------------	----------

### Electrical Specifications

Current Rating	5.0A
Voltage Rating	750V
Contact Resistance	10mΩ
Insulation Resistance	5000MΩ

### Mechanical Specifications

Wire Accommodation	20-24 AWG
--------------------	-----------

### Protection Category

IP Ratings	IP 40
------------	-------

### Approvals

Declarations	MFR Declaration of Conformity
--------------	-------------------------------

