



EN ISO 20345:2011



SKIPPER LADY

BELVEDERE
95416-01
S1 SRC
Size: 35-42 Lady

Weight: 415 gr.

Fit: 11

Working Environment:

 Logistics and Light Industry,
 Components and Automotive, ESD
 Areas


FEATURES

UPPER

 Digitex Airy
 MicroFiber Suede with Pro-tech
 SXT light

LINING

 Breezy 3D, two-layers
 combination

ANTISLIP LINING

DUALMICRO

INSOLE

Five 4 Fit "lady"

TOE CAP

Alu SXT 2.0 Toe cap

TYPE

Sandal

SOLE

PU DUAL-DENSITY SRC

 Double density PU outsole with
 tread designed mainly for indoor
 use. Self-cleaning design and
 highly non-slip grip. SRC Antislip
 standard.

TECHNOLOGIES

Removable Insole

FIVE 4 FIT
 LADY

 Highly breathable and absorbent
 anatomic insole. Multilayer structure
 to take advantage of the peculiarities
 of each component. Dry and with a
 comfortable memory foam "pillow"


Protection elements

alu-sxt 2.0
 aluminium

 The result of the evolution of the
 latest aluminium technologies. A new
 multi-thicknesses toe cap, which
 delivers a highly performing
 protection where needed. Ultralight
 protection, keeping comfortable inner
 volumest.


Lateral stability

dynamic HC control
 technology

 Ergonomic rigid internal structure. It
 houses the heel into the right seat,
 adjusting the foot support and control
 of the ankle sideways movements. It
 keeps the foot tight to the shoe,
 allowing the perfect fit.


Torsional stability

STABIL•ACTIVE

 Support made of rigid plastic
 material. It stabilizes the heel bone,
 the instep and tarsal joints, without
 altering energy absorption. A support
 for the natural movement of the foot;
 it provides comfort and greater
 stability.


Electrical features


 ESD footwear discharge static
 electricity and avoid damaging
 surrounding objects; they are
 designed in compliance with the
 following standards: IEC EN
 61340-5-1:2016 - IEC EN
 61340-4-3:2018 - IEC EN
 61340-4-5:2018.

Other

 Strip with 4 filaments of carbon fiber,
 ensuring proven anti-static properties
 of the footwear over time.


SRC (SRA+SRB)


 SOLE 95
 PU - PU

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32	0.38
	HEEL (CONTACT ANGLE °°) ≥0.28	0.34
SRB STEEL + GLYCEROL	FLAT ≥0.18	0.21
	HEEL (CONTACT ANGLE °°) ≥0.13	0.24

EN ISO 20344:2011