

FEATURES

- Flame retardant
- High tensile strength
- Self-locking design
- Highly durable with excellent chemical resistance

RS PRO Steel Stainless Steel Roller Ball Cable Tie, 125mm x 4.6 mm

RS Stock No.: 123-5036



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

These RS PRO 304 grade stainless steel cable ties are an ideal alternative where Nylon 66 cable ties are not suitable such as harsh environments or places where there is heat. These cable ties have a roller ball design which is self-locking and fast and easy to install. Rollerball ties have a locking ball bearing which grips the tie strap and locks the tie as it is tensioned.

General Specifications


Туре	Roller Ball		
Colour	Steel		
Material	Stainless Steel		
Application	in industries such as: Oil and gas Marine Chemical Maintenance Automotive Solar Ship Building Mining Defence Services		
Resistant To	Chemical and Ultraviolet resistance		
UV Resistant	Yes / No		
Minimum Operating Temperature	-40°C		
Maximum Operating Temperature	300°C		
Fire Behaviour	Halogen		
Quantity	100		

Mechanical Specifications

Length	125mm
Width	4.6mm
Tensile Strength	79kg
Maximum Bundle Strength	25mm

Approvals	
Standards Met	UL





Part No	Colour	Material	UL	Maximum Operating Temperatu re	Туре
400 5004	Self	204 Stainlass Steel			Dollar Doll
123-5034	Colour Self	304 Stainless Steel	UL	+538 °C	Roller Ball
123-5035	Colour	304 Stainless Steel	UL	+538 °C	Roller Ball
	Self				
123-5036	Colour	304 Stainless Steel	UL	+538 °C	Roller Ball
123-5037	Self Colour	304 Stainless Steel	UL	+538 °C	Roller Ball

Part No	Maxim um Bundle Diamet er	Length		Pack Size	Operating Temperature Range	Tensile Strength(factory)
		200				
123-5034	50 mm	mm	4.6 mm	100	-80 to +538 °C	1112 N
	102	360				
123-5035	mm	mm	7.9 mm	50	-80 to +538 °C	1559 N
		125				
123-5036	25 mm	mm	4.6 mm	100	-80 to +538 °C	1112 N
	102	360				
123-5037	mm	mm	4.6 mm	100	-80 to +538 °C	1112 N