

5

4


3

2

1

D

Edge mark on first conductor



C

Wire _____ Tinned copper

Gauge _____ AWG 28/7 0,089 mm²

Voltage rating _____ 300 Vr.m.s

Current rating _____ 1,3 A at 10°C rise above ambient

Capacity unbalanced _____ 45,9 pF/m at 1 MHz

Impedance unbalanced _____ 105 Ω

Propagation delay _____ 4,9 ns/m nominal

Insulation material _____ PVC

Temperature rating _____ -20°C (operating) to +105°C
 _____ -30°C (static)



Flammability rating _____ Flame retardant VW1

Insulation resistance _____ 10 000 MΩ/km

Approval _____ UL AWM style 2651

B

A

				Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	SEK 18 flat cable 6 poles	Maßstab/ Scale 10:1	
				Detail.	20/10/05				JMDR
				Insp.					
				Stand.					
09 18 006 7004	100 m (328 feet)	34400	17/09/07	PK	HARTING EURL F-95972 Paris		TB 09 18 006 700X	Blatt/ Page 1 / 1	
09 18 006 7001	30,48 m (100 feet)	33246	20/10/05	JMDR					
Part number	Length per reel	Mod.	Dot.	Name			Sub.		