



ADJUSTABLE TILTING FAN HEAD
FOR DYNAMIC AIR CIRCULATION



3 SETTINGS FOR VARIABLE FAN SPEED



175CM POWER CABLE CAN BE
STOWED WHEN NOT IN USE

ITEM. 05632

SIP 16" HEAVY-DUTY FLOOR FAN

POWERFUL FLOOR FAN FOR EFFECTIVE AIR CIRCULATION

PRODUCT OVERVIEW

The **SIP 16" Heavy-Duty Floor Fan** uses a 3-blade design to deliver powerful airflow to help cool spaces and circulate air in a variety of indoor environments. Mounted on a sturdy steel frame, the fan can be tilted on it's vertical axis to adjust the airflow and provide outstanding cooling and air circulation coverage. Fans are essential in helping to provide improved air quality to indoor spaces.

FEATURES & BENEFITS

✓ POWERFUL AIRFLOW

A heavy-duty 3-blade fan is powered from a 75w motor to deliver powerful and consistent airflow coverage.

✓ VARIABLE SPEED SETTINGS

3 settings for variable fan speed:

- **Low:** 955rpm
- **Medium:** 1111rpm
- **High:** 1302rpm

✓ TILTING FAN HEAD

The adjustable fan head tilts on it's vertical axis for dynamic circulation of air.
A robust balanced steel frame maintains fan stability when in use.

THIS PRODUCT COMES WITH AN SIP 2-YEAR SILVER WARRANTY*

FIND OUT MORE AT [SIP-GROUP.COM/WARRANTY](https://www.sip-group.com/warranty)



ITEM. 05632

SIP 16" HEAVY-DUTY FLOOR FAN

FEATURES & BENEFITS CONT.

✓ ENHANCED SAFETY FEATURES

Fan blades are fully enclosed with solid mesh steel guarding for greater user safety.

APPLICATIONS & USES

DELIVERS POWERFUL VARIABLE SPEED
AIR CIRCULATION TO INDOOR SPACES

PERFECT FOR INDOOR AREAS SUCH AS OFFICES,
WORKSHOPS OR DOMESTIC USES

ITEM NO.	05632		
INPUT SUPPLY	230v (13A)		
MOTOR POWER	75w (0.1hp)		
POWER CABLE	175cm		
FAN DIAMETER	Ø 16" (406mm)		
SPEED SETTINGS	3 speed settings		
	Low	Medium	High
	955rpm	1111rpm	1302rpm
NOISE LEVEL	60dB(A)		
NET WEIGHT	4.5kg		
GROSS WEIGHT	5.1kg		
PRODUCT DIMENSIONS	540(H) x 530(W) x 220mm(D)		
PACKAGED DIMENSIONS	510(H) x 475(W) x 187mm(D)		