



MULTI-BEAM

TE Internal #: 2-6450880-5
PCB Mount Receptacle, Right Angle, Board-to-Board, 10 Position,
2.54 mm [.1 in] Centerline, Fully Shrouded, Gold (Au), Through Hole
- Press-Fit

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Receptacle**
PCB Mount Orientation: **Right Angle**
Connector System: **Board-to-Board**
Number of Positions: **10**
Number of Rows: **4**

Features

Product Type Features

Mixed & Hybrid Header	Yes
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	4
Number of Loaded Positions	10
Mating & Unmating Configuration	Normal
Number of Signal Positions	8
Number of Power Positions	2
PCB Mount Orientation	Right Angle



Number of Positions	10
Number of Rows	4

Electrical Characteristics

Operating Voltage	60 VDC
-------------------	--------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
PCB Contact Termination Area Plating Material Thickness	.76 – 1.78 µm[30 – 70 µin]
Contact Layout	Matrix
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Receptacle
Contact Current Rating (Max)	50 A

Termination Features

Termination Post & Tail Length	3.02 mm[.119 in]
Termination Method to PCB	Through Hole - Press-Fit

Mechanical Attachment

Mating Alignment Type	Guide Post
PCB Mount Retention Type	Hold-Down
PCB Mount Alignment Type	Hold-Down
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	High Temperature Thermoplastic Glass-Filled
Centerline (Pitch)	2.54 mm[.1 in]



Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Connector Width	20.83 mm[.82 in]
PCB Thickness (Recommended)	1.35 mm[.053 in]
Connector Height	11.94 mm[.47 in]
Connector Length	23.62 mm[.93 in]

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	High Temperature Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	110
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-6450820-4

MBXL VERT HDR 8P + 12S + 6P

Customers Also Bought



TE Part #3-6450170-5

MBXL R/A RCPT 2P+8S+2P



TE Part #6-1879271-4

RP 2A 178R 0.1% 15PPM CUT LENGTH




TE Part #5-1879132-6

RN 0402 34K 0.1% 10PPM 1K RL



TE Part #6600120-2

MBXL R/A HDR DB 24S+6P



TE Part #1926720-2

AssyMINIPAKHDL2p15s2p RAplugBdlk




TE Part #111196-7

030 RCPT SYSTEM 50 30 DPLX



TE Part #5-1437567-2

MPG206NPC=(MSPG) SW P/B DPDT P



TE Part #3-2176074-2

CPF 0201 12K1 0.5% 50PPM 1K RL



TE Part #CAT-SIGH262

Signal Header

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-6450880-5_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-6450880-5_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-6450880-5_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English