

# UM-TMF (5X10) - Marker for terminal blocks



0830930

<https://www.phoenixcontact.com/gb/products/0830930>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker for terminal blocks, Strip, white, unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: latching, Number of individual labels: 24, text field height: 10 mm, text field width: 5 mm



## Your advantages

- The markers, which are supplied in uniform strips, can be printed onto quickly and easily using the BLUEMARK printing systems
- The UM-TMF ... UM labeling range includes terminal markers for Phoenix Contact terminal blocks with flat marker groove
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers support multi-line labeling

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0830930       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BGE21C        |
| Product key                          | BGE21C        |
| GTIN                                 | 4046356910651 |
| Weight per piece (including packing) | 2.12 g        |
| Weight per piece (excluding packing) | 2 g           |
| Customs tariff number                | 39269097      |
| Country of origin                    | PL            |

# UM-TMF (5X10) - Marker for terminal blocks



0830930

<https://www.phoenixcontact.com/gb/products/0830930>

## Technical data

### Product properties

|                     |                 |
|---------------------|-----------------|
| Product type        | Klemmenmarker   |
| Area of application | Phoenix Contact |

### Marking

|                                     |                   |
|-------------------------------------|-------------------|
| Number of individual labels         | 24                |
| Number of individual labels per row | 12                |
| Number of marker strips             | 2                 |
| Identification technology           | UV LED technology |

### Dimensions

|        |          |
|--------|----------|
| Width  | 4.60 mm  |
| Height | 10.47 mm |
| Depth  | 2.40 mm  |

### Material specifications

|  |  |
|--|--|
| RoHS compliant                         | yes                                      |
| Color                                  | white (RAL 9010)                         |
| Flammability rating according to UL 94 | V2                                       |
| Base element material                  | PC                                       |
| Components                             | free from silicone, halogen, and cadmium |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |

#### Wipe resistance of inscriptions

|   |  |
|---|--|
| Specification                                   | IEC 61010-1:2010-06                            |
|   | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                  | Test passed                                    |
| n-Hexane<br>[CAS No. 110-54-3]                  | Test passed                                    |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed                                    |

#### Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |

# UM-TMF (5X10) - Marker for terminal blocks



0830930

<https://www.phoenixcontact.com/gb/products/0830930>

|        |   |
|--------|---|
| Cycles | 2 |
|--------|---|

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |

## Ambient conditions

|   |                   |
|---|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 120 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

## Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

# UM-TMF (5X10) - Marker for terminal blocks



0830930

<https://www.phoenixcontact.com/gb/products/0830930>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000761 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# UM-TMF (5X10) - Marker for terminal blocks



0830930

<https://www.phoenixcontact.com/gb/products/0830930>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.009 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)