


SPEED GRINDING METAL

PRO

- 1 Fast stock removal with ceramic grains
- 2 Vulcanised backing for stable grinding
- 3 Top-size coating for material versatility



* vs Bosch R444



BOSCH

PRO R780 FIBRE DISC

PRO


- For grinding metal, eg when removing welds and stock on mild steel and stainless steel
- Highly efficient for metalworkers: Speed
- Up to 1.9x faster than a Bosch R444 Fibre Disc
- With 22.23 mm bore for standard locking nut angle grinders



PRODUCT PROPERTIES				ORDERING INFORMATION					
Disc diameter mm	Bore diameter mm	Grit	X-LOCK	Packaging type	Pack quantity	Minimum order quantity	Barcode 3 165 140...	Part number	
115	22.23	36	-	S	1	50	915 168	2 608 621 604	
115	22.23	50	-	S	1	50	915 175	2 608 621 605	
115	22.23	60	-	S	1	50	915 182	2 608 621 606	
115	22.23	80	-	S	1	50	915 199	2 608 621 607	
115	22.23	100	-	S	1	50	915 205	2 608 621 608	
115	22.23	120	-	S	1	50	915 212	2 608 621 609	
125	22.23	36	-	S	1	50	915 229	2 608 621 610	
125	22.23	50	-	S	1	50	915 236	2 608 621 611	
125	22.23	60	-	S	1	50	915 243	2 608 621 612	
125	22.23	80	-	S	1	50	915 250	2 608 621 613	
125	22.23	100	-	S	1	50	915 267	2 608 621 614	
125	22.23	120	-	S	1	50	915 274	2 608 621 615	


BOSCH