

# iVu Bar Code Reader (BCR) Image Sensor



## Datasheet

*iVu BCR Image Sensor for use with a Remote Display*

The iVu Series Barcode Reader (BCR) sensor package consists of lighting, sensor, and lens. This version of the iVu BCR requires a separately available Remote Display touch screen to set up and monitor inspections. Appropriate cables and mounting brackets can be ordered for each application. Additionally, other lenses, brackets, filters and external lights are available. Installation, setup, and configuration can be done quickly without requiring a PC to configure the sensor.

### Features

- No PC required to configure the sensor
- Image processing expertise is not required
- USB port for uploading and downloading of inspections and log files for easy updating and diagnostics
- Separate touch screen display mounts remotely from the sensor to allow easy access to the user interface and to view inspection images
- A RS-232 serial communications port that is used to output barcode data to other applications
- High speed processing



The iVu BCR reads the following barcode types:

- DataMatrix (ECC 200) barcodes
- QR Code (QR and Micro QR)
- Linear barcodes: Code128, Code39, CODABAR, Interleaved 2 of 5, EAN13, EAN8, UPCE, Postnet, IMB, and Pharmacode



### WARNING: Not To Be Used for Personnel Protection

Never use this device as a sensing device for personnel protection. Doing so could lead to serious injury or death. This device does not include the self-checking redundant circuitry necessary to allow its use in personnel safety applications. A sensor failure or malfunction can cause either an energized or de-energized sensor output condition.

## Models

NPN Models						
Ring Light Options	Micro Video Lens Options					C-Mount Lens Options
	4.3 mm	8 mm	12 mm	16 mm	25 mm	
None	IVURBNX04	IVURBNX08	IVURBNX12	IVURBNX16	IVURBNX25	IVURBNXC
Red	IVURBNR04	IVURBNR08	IVURBNR12	IVURBNR16	IVURBNR25	N/A
Blue	IVURBNB04	IVURBNB08	IVURBNB12	IVURBNB16	IVURBNB25	N/A
Green	IVURBNG04	IVURBNG08	IVURBNG12	IVURBNG16	IVURBNG25	N/A
IR	IVURBNI04	IVURBNI08	IVURBNI12	IVURBNI16	IVURBNI25	N/A
White	IVURBNW04	IVURBNW08	IVURBNW12	IVURBNW16	IVURBNW25	N/A
UV 365 <sup>1</sup>	IVURBN604	IVURBN608	IVURBN612	IVURBN616	IVURBN625	N/A
UV 395 <sup>1</sup>	IVURBN904	IVURBN908	IVURBN912	IVURBN916	IVURBN925	N/A

<sup>1</sup> Blue Filter Kit (FLT B) included with UV models.



PNP Models						
Ring Light Options	Micro Video Lens Options					C-Mount Lens Options
	4.3 mm	8 mm	12 mm	16 mm	25 mm	
None	IVURBPX04	IVURBPX08	IVURBPX12	IVURBPX16	IVURBPX25	IVURBPXC
Red	IVURBPR04	IVURBPR08	IVURBPR08	IVURBPR16	IVURBPR25	N/A
Blue	IVURBPB04	IVURBPB08	IVURBPB08	IVURBPB16	IVURBPB25	N/A
Green	IVURBPG04	IVURBPG08	IVURBPG08	IVURBPG16	IVURBPG25	N/A
IR	IVURBPI04	IVURBPI08	IVURBPI12	IVURBPI16	IVURBPI25	N/A
White	IVURBPW04	IVURBPW08	IVURBPW12	IVURBPW16	IVURBPW25	N/A
UV 365 <sup>1</sup>	IVURBP604	IVURBP608	IVURBP612	IVURBP616	IVURBP625	N/A
UV 395 <sup>1</sup>	IVURBP904	IVURBP908	IVURBP912	IVURBP916	IVURBP925	N/A



NOTE: This product emits UV light. Exempt Risk Group (RG 0) product. No optical hazard is considered reasonably foreseeable, even for continuous, unrestricted use (IEC 62471).

## Sensor Specifications

### Power Connection

12-pin Euro-style (M12) male connector; accessory cable required for operation (see [Power Cable — Required](#) on page 7)

### USB 2.0 Host

4-pin Pico (M8) female connector; optional USB cable required for operation of USB flash drive (see [USB Cable — Optional](#) on page 8)

### Power Requirements

Voltage: 10 to 30 V dc  
Current: 800 mA maximum (exclusive of I/O load)

### Output Configuration

NPN or PNP determined by model

### Demo Mode

Full tool functionality on canned images

### Sensor Lock

Optional password protection

### External Strobe Output

+ 5 V dc

### Integrated Ring Light

Red, IR, Green, Blue, White

### Output Rating

150 mA

### Remote Display Connection

8-pin Euro-style (M12) female connector; accessory cable required for remote display

### Acquisition

60 fps (frames per second)<sup>2</sup>

### Exposure Time

0.1 ms to 1.049 s

### Imager

1/3 inch CMOS 752 × 480 pixels; adjustable Field of View (FOV)

### Lens Mount

Micro Video Lens models: M12 × 1 mm thread; micro video lens 4.3, 6, 8, 12, 16, 25 mm  
C-Mount models: Standard C-mount (1 inch-32 UN)

### Construction

Black Valox™ sensor housing; acrylic window  
Weight: 0.20 kg (0.45 lbs)

### Environmental Rating

IP67

### Operating Conditions

Stable Ambient Temperature: 0 °C to +50 °C (+32 °F to +122 °F)

Maximum relative humidity: 95% maximum relative humidity (non-condensing)


### Certifications




<sup>2</sup> This value can vary based on inspection settings.

## Dimensions

### Micro Video Lens Dimensions




### C-Mount Lens Dimensions



### Cable Connections for the iVu BCR with a Remote Display

The cable connections on the iVu sensor are shown below, and power I/O connections (B) are defined in the Power I/O Connections table below.



- A Remote Display Connector
- B Power I/O Connector
- C USB Connector



NOTE: Micro video lens model shown. C-Mount model connections are identical.


Power I/O Connections			
Pin #	Wire Color	Description	Direction
1	White	Output 1	Output
2	Brown	10-30V dc	Input
3	Green	Output 2	Output
4	Yellow	Strobe Out (5V dc only)	Output
5	Gray	Remote Teach	Input

Power I/O Connections			
Pin #	Wire Color	Description	Direction
6	Pink	External Trigger	Input
7	Blue	Common (Signal Ground)	Input
8	Red	Ready	Output
9	Orange	Not used	N/A
10	Light Blue	RS-232 TX	Output
11	Black	RS-232 Signal Ground	Output
12	Violet	RS-232 Rx	Input

## iVu Trigger, Remote Teach, and I/O Waveforms


The iVu has two input signals—Trigger and Remote Teach. The default setting is to detect the low to high transition. This setting can be changed in the Main Menu > System > Discrete I/O > Input Polarity screen on the sensor.

### PNP (Low-to-High) Trigger and Remote Teach Input Waveforms



The sensor triggers from low to high, and Remote Teach behaves electrically like trigger.

### NPN (High-to-Low) Trigger and Remote Teach Input Waveforms




The sensor triggers from high to low, and Remote Teach behaves electrically like trigger.



**NOTE:** If the device used to trigger or remote teach the iVu BCR is a sinking device, these are the options regarding the use of a pull-up resistor:

Option 1: Put a pull-up resistor, rated approximately 1k ohm, between the sensor's positive (+) voltage and the sensor's input as shown below.



## iVu Output Waveforms




Figure 1. PNP Outputs






Figure 2. NPN Outputs

## Accessories

### Power Cable — Required

12-Pin M12/Euro-Style Cordsets with Open Shield				
Model	Length	Style	Dimensions	Pinout
MQDC2S-1206	1.83 m (6 ft)	Straight		 <ul style="list-style-type: none"> <li>1 = White</li> <li>2 = Brown</li> <li>3 = Green</li> <li>4 = Yellow</li> <li>5 = Gray</li> <li>6 = Pink</li> <li>7 = Blue</li> <li>8 = Red</li> <li>9 = Orange</li> <li>10 = Lt. Blue</li> <li>11 = Black</li> <li>12 = Violet</li> </ul>
MQDC2S-1215	4.57 m (15 ft)			
MQDC2S-1230	9.14 m (30 ft)			
MQDC2S-1250	15.2 m (50 ft)			
MQDC2S-1275	22.9 m (75 ft)			



NOTE: The cables listed above must be used to meet .

### Remote Display — Required for Setup

Model	Description	Data Sheet
RD35	89 mm (3.5 in) Diagonal Remote Touch Screen	p/n 149171
RDM35	89 mm (3.5 in) Diagonal Machine-Mountable Remote Touch Screen	p/n 166096

## Cordsets



Table 1: Cordsets

Model	Length	Description
IVURD-MX-803	0.91 m (3 ft)	8-pin cable, straight, M12-Molex
IVURD-MX-806	1.83 m (6 ft)	
IVURD-MX-815	4.57 m (15 ft)	
IVURD-MX-830	9.14 m (30 ft)	
IVURD-MX-850	15.2 m (50 ft)	
IVURD-MX-803RA	0.91m (3 ft)	8-pin cable, right-angle, M12-Molex
IVURD-MX-806RA	1.83m (6 ft)	
IVURD-MX-815RA	4.57m (15 ft)	
IVURD-MX-830RA	9.14m (30 ft)	
IVURD-MX-850RA	15.2m (50 ft)	

Table 2: Cordset Kits

Model	Length	Description
IVURD-MXK-803	0.91 m (3 ft)	8-pin cable, straight, M12-Molex Mounting Bracket (SMBRD35) Stylus
IVURD-MXK-806	1.83 m (6 ft)	
IVURD-MXK-815	4.57 m (15 ft)	
IVURD-MXK-830	9.14 m (30 ft)	
IVURD-MXK-850	15.2 m (50 ft)	
IVURD-MXK-803RA	0.91 m (3 ft)	8-pin cable, right-angle, M12-Molex Mounting Bracket (SMBRD35) Stylus
IVURD-MXK-806RA	1.83 m (6 ft)	
IVURD-MXK-815RA	4.57 m (15 ft)	
IVURD-MXK-830RA	9.14 m (30 ft)	
IVURD-MXK-850RA	15.2 m (50 ft)	

### USB Cable — Optional

4-Pin Threaded M8/Pico-Style to USB Cordsets with Shield—Double Ended				
Model	Length	Style	Dimensions	Pinout
PSG-4M-4005-USB	0.15 m (6 in)	Straight Pico QD/ USB		 <p>1 = Red 2 = White 3 = Black 4 = Green</p>
PSG-4M-401-USB	0.31 m (1 ft)			
PSG-4M-403-USB	0.91 m (3 ft)			
PSG-4M-410-USB	3.0 m (10 ft)			
PSG-4M-416-USB	4.9 m (16 ft)			


### USB Flash Drive — Optional

Model	Description
IVU-USBFD2	USB Flash Drive 2 GB

### Brackets


#### SMBIVURAL

- Right-angle bracket for mounting sensor from the left
- 12-ga. stainless steel
- Hardware included




#### SMBIVURAR

- Right-angle bracket for mounting sensor from right
- 12-ga. stainless steel
- Hardware included



SMBIVUU

- U-shaped swivel bracket kit
- 14-ga. stainless steel
- Hardware included



NOTE: Use cables with right-angle connectors with this bracket kit.

## Micro Video Lens Accessories

### Micro Video Lens Models

Model	Lens Description
LMFO4 <sup>3</sup>	4.3 mm lens
LMFO6	6 mm lens
LMFO8	8 mm lens
LMF12	12 mm lens
LMF16	16 mm lens
LMF25	25 mm lens

### Micro Video Lens Filters — Optional

Model	Description
FLTMR	Red filter kit
FLTMB	Blue filter kit
FLTMG	Green filter kit
FLTMI	IR filter kit

## C-Mount Lens Accessories

### C-Mount Lens Models

Model	Lens Description
LCFO4	4 mm Lens - no threads for filter
LCFO8	8 mm Lens - no threads for filter
LCF12	12 mm Lens - no threads for filter
LCF16	16 mm Lens, aperture lock - no threads for filter
LCF25R	25mm lens
LCF25LR	25mm lens with focus locking
LCF50L1R	50mm lens with focus locking, plastic
LCF50L2R	50mm lens with focus locking, metal (will not fit ring)
LCF75LR	75mm lens with focus locking, metal (will not fit ring)

<sup>3</sup> Due to the flexibility of the replaceable lenses, focus mechanism, and imager field-of-view settings, it is possible with the 4.3 mm lens to experience reflections from the internal strobe on the inspection image. To eliminate this effect, the field-of-view can be limited to the system default of 320×240 (or 640×480 for fine), the working distance to the object should be no more than about 8 inches, or an external strobe should be used instead of the internal ring light.

## C-Mount Lens Enclosure Choices

Model	Description
IVUSLC50-P	Sealed C-mount lens enclosure
IVUSLC75-P	

## C-Mount Lens Filters — Optional

Model	Description
FLTR	Red filter kit
FLTB	Blue filter kit
FLTG	Green filter kit
FLTI	IR Filter kit

## Banner Engineering Corp Limited Warranty

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEALING OR TRADE USAGE.

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp.