

EMSP-AL (50X15) - Equipment marking



0830773

<https://www.phoenixcontact.com/gb/products/0830773>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Equipment marking, Aluminum label, aluminum color, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, BLUEMARK E.CARD, mounting type: screw, rivet, Number of individual labels: 1, text field height: 15 mm, text field width: 50 mm



Product description

Note:
Due to the current challenges of the global procurement market, Phoenix Contact has unfortunately been forced to accept an aluminum alloy material quality that may cause the appearance to deviate from the homogenous surface quality that was previously expected. This has no impact on the quality of the aluminum labels themselves or the durability of the printing. The effect is purely visual.

Your advantages

- The markers can be marked quickly, easily, and cost-effectively with the BLUEMARK printing systems
- Aluminum equipment marking for screwing or riveting
- Identification made from metal, high strength in a lightweight design
- Increased durability due to the decoratively anodized surface

Commercial data

Item number	0830773
Packing unit	45 pc
Minimum order quantity	45 pc
Sales key	BG241B
Product key	BG241B
Catalog page	Page 296 (C-3-2019)
GTIN	4046356768801
Weight per piece (including packing)	2.14 g
Weight per piece (excluding packing)	2.18 g
Customs tariff number	76169990
Country of origin	DE

EMSP-AL (50X15) - Equipment marking



0830773

<https://www.phoenixcontact.com/gb/products/0830773>

Technical data

Product properties

Product type	Device marking
Type	single without screws

Marking

Number of individual labels	1
Number of individual labels per row	1
Number of bore holes	2
Identification technology	UV LED technology

Mounting

Mounting type	screw, rivet
---------------	--------------

Material specifications

Color	Aluminum color
Material	Aluminum
Base element material	Aluminum
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

EMSP-AL (50X15) - Equipment marking



0830773

<https://www.phoenixcontact.com/gb/products/0830773>

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

High pressure test

Specification	ISO 20653:2013-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-25 °C ... 120 °C (> +80 °C slight changes of the material surface possible)
Recommended ambient temperature (storage/transport)	5 °C ... 25 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

EMSP-AL (50X15) - Equipment marking



0830773

<https://www.phoenixcontact.com/gb/products/0830773>

Dimensions

Width	60 mm
Length	15 mm
Material strength	0.80 mm

Text field

Text field width	50 mm
Text field height	15 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

EMSP-AL (50X15) - Equipment marking



0830773

<https://www.phoenixcontact.com/gb/products/0830773>

Classifications

ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EMSP-AL (50X15) - Equipment marking



0830773
<https://www.phoenixcontact.com/gb/products/0830773>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk