

ATP - PROTWIST® screwdrivers for Phillips® screws - short blades




Standards:

**NF ISO 8764-1, NF ISO 8764-2,
ISO 8764-1, ISO 8764-2, DIN ISO
8764-1, DIN ISO 8764-2, ASME
B107.600**

Description:

- Short blade and ball handle for use in confined spaces.
- Inline Hardening Process – +50% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Blade " tri-coating " treatment (Zinc-Nickel-Chromium) - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.

	Diameter [mm]	Diameter D1 [mm]	Length L1 [mm]	Length L [mm]	Length L2 [mm]	Weight [g]	Phillips Tip Number ["]
ATP1X25	36.0	4.5	25.0	81.0	56.0	38.0	PH1
ATP1X25PB	36.0	4.5	25.0	81.0	56.0	38.0	PH1
ATP1X35	36.0	4.5	35.0	91.0	56.0	39.0	PH1
ATP2X35	36.0	6.0	35.0	91.0	56.0	44.0	PH2
ATP2X35PB	36.0	6.0	35.0	91.0	56.0	44.0	PH2