

Harmony XB5, Flush mounted push button head, plastic, red, Ø30, spring return, unmarked, grey bezel

ZB5FA4C0

EAN Code: 3606489771188

Main

Range of product	Harmony XB5	
Product or component type	Head for non-illuminated push-button	
Device short name	ZB5	
Product compatibility	ZBYF ZBZF32 ZBZF33 ZB5AZ	
Bezel material	Plastic colour plated grey	
Mounting diameter	30.5 mm	
Head type	Built-in-flush	
Sale per indivisible quantity	1	
Shape of signaling unit head	Round	
Type of operator	spring return	
Operator profile	Red flush, unmarked	

Complementary

CAD overall width	37 mm
CAD overall height	37 mm
CAD overall depth	30 mm
Net weight	0.03 kg
Mechanical durability	10000000 cycles
Electrical composition code	C1 for <9 contacts using single blocks in front mounting C2 for <9 contacts using single and double blocks in front mounting C11 for <3 contacts using single blocks in front mounting C15 for <1 contacts using single blocks in front mounting SF1 for <3 contacts using single blocks in front mounting
Device presentation	Basic element

Environment

Protective treatment	тн
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-4070 °C
Overvoltage category	Class II conforming to IEC 60536
IP degree of protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529

Resistance to high pressure washer	7000000 Pa at 55 °C, distance : 0.1 m	
IK degree of protection	IK03 conforming to IEC 50102	
Standards	IEC 60947-5-4 CSA C22.2 No 14 IEC 60947-1 UL 508 JIS C8201-5-1 IEC 60947-5-1 JIS C8201-1	
Product certifications	CSA DNV BV LROS (Lloyds register of shipping) UL listed	
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 25 gn (duration = 6 ms) for 1000 shocks on each axis conforming to IEC 60068-2-27	
Vibration resistance	5 gn (f= 10500 Hz) conforming to IEC 60068-2-6 2 mm peak to peak (f= 210 Hz) conforming to IEC 60068-2-6	

Packing Units

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.45 cm
Package 1 Width	4.3 cm
Package 1 Length	5.2 cm
Package 1 Weight	23.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	80
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.295 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No