



Chemical protection

ULTRANITRIL 485

Frequent contact | intermittent wear

Good sensitivity for standard chemical protection



CHEMICAL PROTECTION
TYPE B

EN388



3101X

EN ISO 374-1



TYPE B
JKOPT

EN ISO 374-5



VIRUS

CATEGORY 3

DEXTERITY

EN ISO 21420:
5/5



ISO 18889



0334

SPECIFIC ADVANTAGES



Comfort

- Excellent dexterity, due to the suppleness of the glove



Productivity

- Good grip on slippery objects, due to the embossed texture



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Care for the environment

- Recycled material in the packaging: 30 %

INDUSTRIES

- Automotive/mechanical industry
- Chemical industry
- Other industries
- Agriculture sector

APPLICATIONS

- Spray mixtures preparation
- Pesticides handling
- Tank filling
- Application & spreading of pesticides
- Pesticides waste management
- Treatment equipment cleaning
- Manufacture and application of paints and varnishes
- Application of phytosanitary products
- Maintenance
- Timber treatment and finishing



Chemical protection

ULTRANITRIL 485

Frequent contact | intermittent wear

LEGENDS

EN388	MECHANICAL HAZARDS
3 1 0 1 X	PERFORMANCE LEVELS (X = NOT TESTED)
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN ISO 374-1	CHEMICAL RISKS
TYPE B	J: n-Heptane K: Sodium hydroxide 40% O: Ammonia 25% P: Hydrogen peroxide 30% T: Formaldehyde 37%
G2	PROTECTION FROM PESTICIDES
ISO 18889	G2: Diluted & concentrated pesticides / Mechanical risk
EN ISO 374-5	MICRO-ORGANISMS
VIRUS	Protection against bacteria, fungi and virus

PRODUCT DETAILS

Interior finish	Flocked
Exterior finish	Embossed texture
Material	Nitrile
Cuff characteristic	Straight cuff
Colour.s	Green
Length (cm)	31
Thickness (mm)	0.34
European sizes	7 8 9 10

LOGISTIC DETAILS

Packaging	12 pairs/bag 72 pairs/carton
-----------	---------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/10/18/2079
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France

Edit 09/12/2024