

APC Smart-UPS On-Line, 3kVA, Tower, 208V/230V, 6x C13+2x C19 IEC outlets, SmartSlot, Extended runtime, W/O rail kit

SRT3000XLW-IEC

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.	
Lead time	Usually in Stock	
Main		
Main Input Voltage	208 V	
	230 V	
Product or Component Type	Uninterruptible power supply (UPS)	
Other Input Voltage	220 V	
	240 V	
Main Output Voltage	208 V	
	230 V	
Other Output Voltage	220 V	
	240 V	
Kw Rating	2700 W	
rated power in VA	3000 VA	
Input Connection Type	BS1363A British	
	IEC 60320 C20	
	Schuko CEE 7 / EU1-16P	
output connection type	6 IEC 60320 C13	
	2 IEC Jumpers	
	2 IEC 60320 C19	
Cable length	8 ft (2.4 m)	
Number of cables	3	
Provided equipment	CD with software	
	Documentation CD	
	Installation guide	
	Removable support feet	
	Smart UPS signalling RS-232 cable	
	USB cable	
Range of Product	Smart-UPS On-Line	

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery Type	Lead-Acid battery
Battery Voltage	96V
Extendable Run Time	1
Included Battery Modules	1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

3 h
1
35 year(s)
APCRBC152 ☐
168 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	High density
Redundant	No
Topology	Double Conversion Online

Physical

,	
color	Black
Height	17.01 in (43.2 cm)
Width	3.35 in (8.5 cm)
Depth	25.00 in (63.5 cm)
Net Weight	69.005 lb(US) (31.3 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Mounting position	Vertical

Input

Efficiency at full load	100275 V adjustable (half load)
Input Frequency	40 - 70 Hz auto-sensing

Output

Bypass type	Internal Bypass (Automatic and Manual)
Crest factor	3:1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	3000 VA
Max Configurable Power (Watts)	2700 W
Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Additional information	Configurable for 220 : 230 or 240 nominal output voltage

Conformance

Product Certifications	CE EAC ENERGY STAR V2.0 (USA) RCM VDE UK PSTI
Marking	CE Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic level	55 dBA
Online Thermal Dissipation	703 Btu/h
Operating altitude	010000 ft
Ambient air temperature for operation	32104 °F (040 °C)
Ambient Air Temperature for Storage	5113 °F (-1545 °C)
Storage altitude	050000 ft (0.000000000015240.0000000000 m)
IP degree of protection	IP20
Relative Humidity	095 % non-condensing
Storage Relative Humidity	095 % non-condensing

Communications & Management

Emergency Power Off (EPO)	Yes
Free slots	1
Alarm	Audible and visible alarms : prioritized by severity

Surge Protection and Filtering

Surge energy rating 340 J

Ordering and shipping details

GTIN	731304320081	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.69 in (24.6 cm)
Package 1 Width	34.29 in (87.1 cm)
Package 1 Length	23.58 in (59.9 cm)
Package 1 Weight	81.00 lb(US) (36.74 kg)

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	4962
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	4282bd22-a353-4f82-bb5c-97bbd7f1d1e9
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
[™] Energy efficiency	
Optimized Energy Efficiency	Energy efficient product
ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.