

FEATURES

- Yellow reinforced flexible PVC tubing
- UV resistant
- DEHP and Phthalate Free
- Highly flexible – ease of handling
- Abrasion and kink resistance
- Ultra smooth liner ensuring water flow performance
- Resistant to repeated pulling, bending, crushing
- Working Temperature range - 15°C to +65°C
- 3:1 safety factor

RS PRO PVC Flexible Tubing, Yellow, 25.5mm External Diameter, 50m Long, Reinforced, 160mm Bend Radius, Water

RS Stock No.: 917-5128



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This yellow PVC flexible tubing from the RS PRO range is the ideal choice for heavy-duty watering and irrigation. The inner core has been designed to optimise water flow while the outer shell is resistant to abrasion, UV and crushing.

General Specifications

Material	PVC
Colour	Yellow
Reinforced	Yes
Nominal Size	19MM x 25.5mm
Application	Water, Farms, Agriculture, Horticulture, Fruit growers, Vegetable growers, Garden Centres and Nurseries, Golf clubs, Sports clubs, Landscapers, Water delivery for Industry, Construction, Local Authorities, Gardening

Mechanical Specifications

Inner Diameter	19mm
Outer Diameter	25.5mm
Length	50m
Bend Radius	160mm
Safety Factor	3:1
Wall Thickness	3.25mm

Operation Environment Specifications

Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+65°C
Maximum Working Pressure	39bar
Maximum Burst Pressure	39bar



Specification:

RS Stock Number	Internal Diameter	External Diameter	Length	Wall Thickness	Max Working Pressure	Burst Pressure	Bend Radius
9175119	12.5 mm	17.5 mm	25 m	2.5 mm	16 bar	48 bar	100 mm
9175112	19 mm	25.5 mm	25 m	3.25 mm	39 bar	39 bar	160 mm
9175116	25 mm	32.5 mm	25 m	3.75 mm	24 bar	24 bar	200 mm
9175125	12.5 mm	17.5 mm	50 m	2.5 mm	16 bar	48 bar	100 mm
9175128	19 mm	19 mm	50 m	3.25 mm	39 bar	39 bar	160 mm
9175122	25 mm	32.5 mm	50 m	3.75 mm	24 bar	24 bar	200 mm