

ZCE05

limit switch head ZCE - without lever spring return
left or right actuation



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Rotary head
Product compatibility	XCKT XCMD XCKP XCKD
Associated lever	ZCY18 ZCY26 ZCY59 ZCY19 ZCY25 ZCY12 ZCY15 ZCY22 ZCY54 ZCY55 ZCY17 ZCY48 ZCY69 ZCY44 ZCY45 ZCY49 ZCY46 ZCY53 ZCY91 ZCY16 ZCY39 ZCY23 ZCY81
Associated body	ZCP26 ZCMD21L08U78 ZCP29 ZCT25P16 ZCMD21M12

ZCMD21L08R12
 ZCP29M12
 ZCMD41L1
 ZCP21
 ZCMD25L1
 ZCD31
 ZCMD81L5
 ZCD35
 ZCT25G11
 ZCMD25L5
 ZCD27
 ZCMD69C12
 ZCMD37L2
 ZCMD61C12
 ZCD28
 ZCT28N12
 ZCD21
 ZCMD29L5
 ZCMD21L5
 ZCMD37L5
 ZCMD39L2
 ZCP39
 ZCP27
 ZCD26
 ZCT27N12
 ZCMD29L1
 ZCP35
 ZCT27G11
 ZCMD81L1
 ZCMD37L1
 ZCT21P16
 ZCD29M12
 ZCP31
 ZCMD41L2
 ZCD39
 ZCMD39L5
 ZCT25N12
 ZCT28G11
 ZCP28
 ZCT27P16
 ZCMD21L1
 ZCT28P16
 ZCD29
 ZCP25
 ZCMD25L2
 ZCT26N12
 ZCD37
 ZCD21M12
 ZCMD29L2
 ZCP21M12
 ZCP37
 ZCT26P16
 ZCT21N12
 ZCMD29C12
 ZCMD61M12
 ZCT26G11
 ZCMD21L2
 ZCMD39L1
 ZCMD21C12
 ZCT21G11
 ZCMD41L5
 ZCD25
 ZCMD81L2

Movement of operating head	Rotary
Type of operator	Without operating lever spring return metal
Type of approach	Lateral approach, 1 or 2 programmable direction

Complementary

Positive opening	With
Net weight	0.045 kg

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------