

WHL-L-T5-308

Trolley workster highline with tool assortment

308 pieces

Code

3082113

EAN

4010886950845

Country of origin

Germany

Customs tariff number

82060000

ETIM

EC000149

UNSPSC

56-12-18-02

eCl@ss

21-07-11-00



Article description

- 308 piece assortment for industry, trade and automotive
- Tools in metric dimensions
- GEDORE Check Tool System: completeness check using 2-colour foam inserts
- In tool trolley WHL-L7

Article parts list

1/4" Reversible ratchet No. 2093 U-20, 1/4" Wobble extension No. 2090 KR-4, 1/4" T-handle No. 2087, 1/4" Socket UD-profile No. D 20 4 5 5.5 6 7 8 9 10 11 12 13, 1/4" Socket insert No. TX 20 E4 E5 E6 E7 E8 E10, 1/4" Screwdriver bit slotted No. 680 4 5.5 6.5 8, 1/4" Screwdriver bit hex No. 685 2.5 3 4 5 6, 1/4" Screwdriver bit XZN No. 685 X 5 6 8, 1/4" Screwdriver bit PH No. 690 1 2 3, 1/4" Screwdriver bit PZ No. 690 PZD 1 2 3, 1/4" Screwdriver bit TX No. 687 TX T6 T7 T8 T9 T10 T15 T20 T25 T27 T30 T40, 1/4" Multi handle No. 676, 1/4" Bit holder No. 699, 1/2" Reversible ratchet No. 1993 U-20, 1/2" Extension No. 1990-21/2, 1/2" Wobble extension No. 1990 KR-5 -10, 1/2" Socket No. D 19 10 11 12 13 14 15 16 17 18 19 21 22 24 27 30 32, 1/2" Screwdriver socket in-hex No. IN 19 5 6 7 8 9 10 12 14, 1/2" Screwdriver socket XZN No. INX 19 6 8 10 12, 1/2" Screwdriver socket in-hex No. IN 19 L 5-90 6-90 8-90 10-140 12-140 14-140, long, 1/2" Screwdriver socket TX No. ITX 19 T20 T25 T27 T30 T40 T45 T50 T55 T60, 1/2" Screwdriver socket TX No. ITX 19 L T20-100 T25-100 T27-100 T30-100 T40-100 T45-100 T50-100 T55-100 T60-100, long, 1/2" Impact socket bit with protective sleeve No. K 19 L5 17 19 21, 5/16" Screwdriver bit slot No. 880 7 8 9 12 ST-40, 5/16" Screwdriver bit in-hex No. 885 5 6 8 10, 5/16" Screwdriver bit PH No. 890 1 2 3 4, 3/8" Reversible ratchet No. 3093 U-20 Recoilless hammer No. 248, 3/8" Cardan extension No. 3090 KR-5 -10, 3/8" Socket wrench UD-profile No. D 30 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 24, 3/8" Screwdriver socket in-hex No. IN 30 5 6 7 8 10, 3/8" Screwdriver socket XZN No. INX 30 5 6 8 10, 3/8" Screwdriver socket TX No. ITX 30 T20 T25 T27 T30 T40 T45 T50, Insert holder 1/4" hexagon - 1/4" square No. 673 6, 3, Bit-Adapter 1/4" hexagon - 1/4" square No. 620, Adaptor 5/16" hexagon - 1/2" square No. KB 819, Open-end spanner with ring ratchet UD-profile No. 7 R 8 10 12 13 14 15 16 17 18 19, Combination spanner UD-profile No. 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 24, Double open-end spanner No. 6 6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 24x27, Double ring-end spanner UD-profile No. 2 6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22, Double ring-end spanner hexagon No. 400 8x10 10x11 12x14 13x15 17x19, open, Offset screwdriver set No. PH 42-88 (2-10 mm), Offset screwdriver set No. H 43 TX-09, 3C-Screwdriver slotted No. 2154SK 3.5 5.5 6.5 8, 3C-Screwdriver PH No. 2160SK PH 12, 3C-Screwdriver TX No. 2163 TX T10 T15 T20 T25 T30 T40, Socket wrench with 3C handle hexagon No. 2133 5.5 6 7 8 9 10, Universal pliers No. 142 10 TL, Power combination pliers No. 8250-180 JC, Multiple pliers No. 8133-200 JC, Power side cutters No. 8316-180 JC, Circlip pliers for external retaining rings No. 8000 A 1 A 2 A 21, Circlip pliers for internal retaining rings No. 8000 J 1 J 2 J 21, Engineer's hammer No. 4 E-500, Centre punch No. 100-12, Pin punch No. 119-15 -3 -4, Flat chisel No. 97-250, Cross-cut chisel No. 98-125, Drift punch No. 99 12-5, Twist drill set No. 8550-024, Hacksaw No. 407, Grip pliers 10" No. 137 10, Steel tape measure, 5m No. 4534-5, Screw remover 1/2" No. K 1900, Cable knife No. 0063-08, Wire brush No. 646, Pocket vernier calipe No. 710, Key file set No. 8728, Bolt extractor set No. 8551-55, Gasket scraper No. 133 K, Feeler gauge set, fan pattern No. 702 20 M

Article information

Contents (Qty of pieces)	308	Material	Sheet steel
Net weight [kg]	112.6 kg	Storage	Tool trolley
Total length [mm]	785 mm	Number of drawers	7
Total width [mm]	510 mm	Drawer type	7 drawers: 5x Type 1, H = 80 mm 2x Type 2, H = 160 mm
Total height [mm]	1.045 mm	Single pull-out stop	no