

Product Search Data Sheet

NCU18XH103F6SRB


In Production Recommended AEC-Q200 RoHS REACH

Applications

Unsuitable	Please be sure to read and comply with
Applications	these "Precautions for use."
Specific Applications	Automotive powertrain/safety equipment
	Please refer to Our Website and
	specifications, etc. for information about
	the performance, functions, quality,
	management, and safety required for
	the above applications, and use
	Products after confirming the
	performance and reliability of the actual
	Product.

Appearance & Shape






Note: This datasheet may be out of date. Please download the latest datasheet of NCU18XH103F6SRB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=NCU18XH103F6SRB

Packaging Information

Packaging	Specifications	Standard Packing Quantity
RB	180mm Paper Tape	4000



- 1. Excellent solderability and high stability in environment
- 2. Excellent long time aging stability
- 3. High accuracy in resistance and B-constant
- 4. Flow / Reflow soldering possible

5. Same B-Constant in the same resistance in the three sizes (0603 size / 0402 size)

- Easy to use smaller size in the circuits
- 6. Lead is not contained in the product.
- 7. UL/cULcertified product.(UL1434, File No. E137188)

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





NCU18XH103F6SRB

Note: This datasheet may be out of date. Please download the latest datasheet of NCU18XH103F6SRB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=NCU18XH103F6SRB

Specifications

Resistance (25°C)	10kΩ
Resistance Value Tolerance (at 25°C)	±1%
B-Constant (25/50°C)	3380K
B-Constant (25/50°C) Tolerance	±1%
B-Constant(25/80°C) (Reference Value)	3428K
B-Constant(25/85°C) (Reference Value)	3434K
B-Constant(25/100°C) (Reference Value)	3455K
Max. Voltage	5V
Maximum Operating Current (25°C)	0.1mA
Typical Dissipation Constant (25℃)	1mW/°C
Operating Temperature Range	-55°C to 150°C
Size Code (in mm)	1.6x0.8mm
Size Code (in inch)	0.6x0.3inch
Shape	SMD
Mass	0.0047g
MSL	1

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.






Product Search Data Sheet

NCU18XH103F6SRB


Note: This datasheet may be out of date. Please download the latest datasheet of NCU18XH103F6SRB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=NCU18XH103F6SRB






Resistance-Temperature Characteristics



Max. Voltage, Max. Operating Voltage/Current Reduction Curve



Temperature Error Characteristics

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering

